019-8012 through 019-8015

4-Person Rope HLL: Cross Arm Straps

FEATURES:

- 4-Person HLL System
- Available in lengths from 30' to 100'
- Rugged double braid rope
 Tensile Strength: 11,562 lbs.
- Rope tensioner with convenient built-in wrench
- · Swivel connection point eliminates twisted rope
- · Convenient carry and storage bag

PERSONAL ATTACHMENT POINT(S)

• 4 O-rings

Minimum breaking strength: 5,000lbs

SYSTEM ATTACHMENT POINT(S)

· 2 Carabiners

Gate rating: 3,600 lbs.

Minimum breaking strength: 5,000 lbs.

2 Cross arm straps

Minimum breaking strength: 5,000 lbs.

ITEM WEIGHT:

· Weight varies per length



USER WEIGHT CAPACITY		
ANSI	130-310 lbs. (140.6 kg) per person; 4 Person maximum	
OSHA	Up to 420 lbs. (190.5 kg) per person; 2 Person maximum	

SIZE(S)			
019-8012	30 Feet (16.5 lbs.)		
019-8013	60 Feet (20.5 lbs.)		
019-8014	80 Feet (23.1 lbs.)		
019-8015	100 Feet (25.7 lbs.)		

STANDARD COMPLIANT WITH		
ANSI	N/A	
OSHA	1926.502, 1910.140, 1910.66	

COMPONENT	MATERIAL SPECIFICATION
Rope	16mm Polyester double braid rope
Rope tensioner	Aluminum with wrench
O-rings	Zinc plated alloy steel
Carabiners	Zinc plated alloy steel
Bag	Polyester
Cross-arm strap	Polyester webbing with Zinc plated alloy steel