



## 021-1433 through 021-1439

### PRO+ Construction Harness: 3D, QC Chest, TB Legs

#### FEATURES :

- Dorsal D-ring
- Dorsal SRL link
- Quick-connect chest
- Quick torso adjusters
- Tongue buckle legs
- Shoulder pad
- Fixed comfort waist pad
- Removable leg pads

#### FALL ARREST POINT(S) :

- 1 Dorsal D-ring
- 1 Dorsal SRL link

#### ITEM WEIGHT :

- 5.1 lbs. (2.3 kg)



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-140.6 kg)
OSHA	Up to 420 lbs. (190.5 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.11-2021
OSHA	1926.502, 1910.140

SIZE(S)	
021-1433	X-Small
021-1434	Small
021-1435	Medium
021-1436	Large
021-1437	X-Large
021-1438	2X
021-1439	3X

COMPONENT	MATERIAL SPECIFICATION
Webbing	Polyester
D-ring	Zinc plated alloy steel
Adjuster buckles	Anodized aluminum
Chest connection	EP alloy steel
Leg connection	Steel tongue buckle w/ SS grommets
Dorsal SRL link	Polyester
Pads	Nubuck synthetic; Polyester mesh; EVA
Belt	Polyester; Steel; Stainless steel