

QUA-016, rev.: 00

OUTDOOR EXTENSION CORD WITH RUGGED SAFETY SEAL LOCK



<p>ELECTRICAL AND STRUCTURAL CHARACTERISTICS.</p>	<p>Cord / Cable: - Type: SJTW 14AWG X 3C (14 AWG=2,08 mm² 3 conductors), 300 V, 105 °C - Length: 50 ft. (15.25 m)</p> <p>Plug: NEMA 5-15P (2 P + Ground Polarized) Socket: NEMA 5-15R (2 P + Ground Polarized)</p> <p>Current: 15 A Voltage: 125 V AC Maximum Power: 1875W Insulated for 300V cable</p>
<p>MATERIALS</p>	<p>Base: ABS/PC Waterproof Cover: PP Contacts: Brass Cord Insulation jacket: Thermoplastic</p>
<p>DEGREE OF PROTECTION</p>	<p>IP67 (IEC 60529) NEMA 4X</p>
<p>IMPACT RESISTANCE</p>	<p>IK07 (IEC 62262)</p>
<p>GLOW WIRE TEST</p>	<p>Live parts supports 750 °C Other parts 650 °C</p>
<p>BALL PRESSURE TEST</p>	<p>Live parts supports 125 °C</p>
<p>APPLIED STANDARD</p>	<p>UL STD. 817 CSA Std. C22.2 NO.21</p>
<p>DIMENSIONS</p>	<p>Power Shell: 9.05" x 2.16" (22.99 cm x 5.49 cm)</p>
<p>WEIGHT</p>	<p>3 lb (1.36 kg)</p>
<p>DIELECTRIC STRENGTH</p>	<p>1250Vac</p>
<p>INSULATION RESISTANCE</p>	<p>>100Mohms</p>

