

### TECHNICAL DATA



### Features

#### Model R2300 Infrared Thermometer

- Built-in laser pointer identifies target area
- User selectable °F or °C
- 12:1 distance to spot size ratio
- Digitally adjustable emissivity
- Max and Min readings
- Backlit display
- High and low alarms
- Low battery indication and auto shut off
- Includes battery

#### Model R6018 Dual Moisture Meter

- Pin and Pinless functions detect moisture in wood and building materials (sheet rock, cardboard, plaster, concrete and mortar)
- Pinless measurement depth up to 1" (25mm)
- Classifies moisture status as: low, medium and high
- Audible alert and Data Hold functions
- Built-in measurement verification and battery check
- Low battery indicator and auto shut-off
- Replaceable pins
- Includes pins, protective cap and battery

#### Model R5210 Receptacle Tester with GFCI

- Compact design
- Detects most common 3-wire receptacle issues
- LED indicators identify 5 wiring faults
- Status indicator chart
- GFCI trip test

#### Model R1910 Compact Temperature & Humidity Meter

- Measures ambient temperature and relative humidity
- Designed for one-handed operation
- Backlit dual LCD display
- User selectable °F/°C
- Max, min and data hold functions
- Low battery indicator and auto shut off
- Includes batteries

#### Model R5110 Non-Contact Voltage Detector with Flashlight

- Suitable for receptacles or against insulated wire
- Double insulated housing for increased safety
- Audible (buzzer) and visual (LED) indicators
- Built-in flashlight
- Pocket clip
- Auto shut off
- Cat. IV 1000V safety rating
- Includes batteries

#### Model R9940 Hard Shell Carrying Case

- Hard outer shell protects items
- Accommodates small to medium sized instruments
- Built-in compartment stores instrument accessories
- Soft interior lining
- External dimensions: 8.75 x 6.5 x 2.25" (222.25 x 165.10 x 57.15mm)

Model	Description
RINSPECT-KIT	Home Inspection Kit