



SAFETY DATA SHEET

1. Identification

Product identifier	Superscope II	
Other means of identification		
Product code	F209022,25,38	
Recommended use	Floor Stripper	
Recommended restrictions	None known.	
Manufacturer/Importer/Supplier/Distributor information		
Manufacturer		
Company name	Franklin Cleaning Technology	
Address	One Fuller Way Great Bend, KS 67530 United States	
Telephone	Customer Service	(800) 810-4829
E-mail	Not available.	
Emergency phone number	CHEMTREC	(800) 424-9300
	Emergency	(620) 792-1711
	24 hour Emergency	(800) 424-9300

2. Hazard(s) identification

Physical hazards	Not classified.	
Health hazards	Acute toxicity, oral	Category 4
	Acute toxicity, inhalation	Category 4
	Skin corrosion/irritation	Category 1
	Serious eye damage/eye irritation	Category 1
	Specific target organ toxicity, single exposure	Category 3 respiratory tract irritation
Environmental hazards	Hazardous to the aquatic environment, acute hazard	Category 2
	Hazardous to the aquatic environment, long-term hazard	Category 2
OSHA defined hazards	Not classified.	

Label elements



Signal word	Danger
Hazard statement	Harmful if swallowed. Causes severe skin burns and eye damage. Causes serious eye damage. Harmful if inhaled. May cause respiratory irritation. Toxic to aquatic life. Toxic to aquatic life with long lasting effects.
Precautionary statement	
Prevention	Do not breathe mist or vapor. Wash thoroughly after handling. Do not eat, drink or smoke when using this product. Use only outdoors or in a well-ventilated area. Avoid release to the environment. Wear protective gloves/protective clothing/eye protection/face protection.
Response	If swallowed: Rinse mouth. Do NOT induce vomiting. If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower. If inhaled: Remove person to fresh air and keep comfortable for breathing. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a poison center/doctor. Specific treatment (see this label). Wash contaminated clothing before reuse. Collect spillage.
Storage	Store in a well-ventilated place. Keep container tightly closed. Store locked up.

Disposal	Dispose of contents/container in accordance with local/regional/national/international regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	4.33% of the mixture consists of component(s) of unknown acute oral toxicity.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
BUTOXYETHANOL		111-76-2	3 - < 5
2-AMINOETHANOL		141-43-5	1 - < 3
ETHYLENE GLYCOL PHENYL ETHER		122-99-6	1 - < 3
NONOXYNOL-9		9016-45-9	1 - < 3
POTASSIUM HYDROXIDE		1310-58-3	1 - < 3
SODIUM METASILICATE		6834-92-0	1 - < 3
Other components below reportable levels			80 - < 90

*Designates that a specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Oxygen or artificial respiration if needed. Call a POISON CENTER or doctor/physician if you feel unwell.
Skin contact	Take off immediately all contaminated clothing. Rinse skin with water/shower. Call a physician or poison control center immediately. Chemical burns must be treated by a physician. Wash contaminated clothing before reuse.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Call a physician or poison control center immediately.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	Burning pain and severe corrosive skin damage. Causes serious eye damage. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Permanent eye damage including blindness could result. May cause respiratory irritation.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Chemical burns: Flush with water immediately. While flushing, remove clothes which do not adhere to affected area. Call an ambulance. Continue flushing during transport to hospital. Keep victim warm. Keep victim under observation. Symptoms may be delayed.
General information	If you feel unwell, seek medical advice (show the label where possible). Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Show this safety data sheet to the doctor in attendance.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO ₂).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire-fighting equipment/instructions	Move containers from fire area if you can do so without risk.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Wear appropriate protective equipment and clothing during clean-up. Do not breathe mist or vapor. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
--	---

Methods and materials for containment and cleaning up

This material is classified as a water pollutant under the Clean Water Act and should be prevented from contaminating soil or from entering sewage and drainage systems which lead to waterways.

Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Cover with plastic sheet to prevent spreading. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.

Environmental precautions

Avoid release to the environment. Contact local authorities in case of spillage to drain/aquatic environment. Prevent further leakage or spillage if safe to do so. Do not contaminate water. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling

Do not breathe mist or vapor. Do not get in eyes, on skin, or on clothing. Avoid prolonged exposure. Do not taste or swallow. When using, do not eat, drink or smoke. Use only outdoors or in a well-ventilated area. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Observe good industrial hygiene practices. Avoid release to the environment. Do not empty into drains.

Conditions for safe storage, including any incompatibilities

Store locked up. Store in original tightly closed container. Store in a well-ventilated place. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
2-AMINOETHANOL (CAS 141-43-5)	PEL	6 mg/m3
BUTOXYETHANOL (CAS 111-76-2)	PEL	3 ppm 240 mg/m3
		50 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
2-AMINOETHANOL (CAS 141-43-5)	STEL	6 ppm
	TWA	3 ppm
BUTOXYETHANOL (CAS 111-76-2)	TWA	20 ppm
POTASSIUM HYDROXIDE (CAS 1310-58-3)	Ceiling	2 mg/m3

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
2-AMINOETHANOL (CAS 141-43-5)	STEL	15 mg/m3
	TWA	6 ppm 8 mg/m3
BUTOXYETHANOL (CAS 111-76-2)	TWA	3 ppm 24 mg/m3
POTASSIUM HYDROXIDE (CAS 1310-58-3)	TWA	5 ppm 2 mg/m3

Biological limit values

ACGIH Biological Exposure Indices

Components	Value	Determinant	Specimen	Sampling Time
BUTOXYETHANOL (CAS 111-76-2)	200 mg/g	Butoxyacetic acid (BAA), with hydrolysis	Creatinine in urine	*

* - For sampling details, please see the source document.

Exposure guidelines

US - California OELs: Skin designation

BUTOXYETHANOL (CAS 111-76-2) Can be absorbed through the skin.

US - Minnesota Haz Subs: Skin designation applies

BUTOXYETHANOL (CAS 111-76-2) Skin designation applies.

US - Tennessee OELs: Skin designation

BUTOXYETHANOL (CAS 111-76-2) Can be absorbed through the skin.

US NIOSH Pocket Guide to Chemical Hazards: Skin designation

BUTOXYETHANOL (CAS 111-76-2) Can be absorbed through the skin.

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

BUTOXYETHANOL (CAS 111-76-2) Can be absorbed through the skin.

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower must be available when handling this product.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles) and a face shield.

Skin protection

Hand protection Wear appropriate chemical resistant gloves.

Other Wear appropriate chemical resistant clothing. Use of an impervious apron is recommended.

Respiratory protection In case of insufficient ventilation, wear suitable respiratory equipment. Chemical respirator with organic vapor cartridge.

Thermal hazards Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

Keep away from food and drink. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance	Liquid.
Physical state	Liquid.
Form	Liquid.
Color	Light orange.
Odor	Matches to Standard
Odor threshold	Not available.
pH	12.8 - 13.9
Melting point/freezing point	Not available.
Initial boiling point and boiling range	212 °F (100 °C)
Flash point	> 212.0 °F (> 100.0 °C)
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.

Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	0.00001 hPa estimated
Vapor density	Not available.
Relative density	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Density	8.80 lbs/gal estimated
Flammability class	Combustible IIIB estimated
Percent volatile	86.5 % estimated
Specific gravity	1.05 estimated
VOC (Weight %)	6.6 % estimated

10. Stability and reactivity

Reactivity	Reacts violently with strong acids. This product may react with oxidizing agents.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	Hazardous polymerization does not occur.
Conditions to avoid	Do not mix with other chemicals. Contact with incompatible materials.
Incompatible materials	Acids. Oxidizing agents.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Ingestion	Causes digestive tract burns. Harmful if swallowed.
Inhalation	Harmful if inhaled.
Skin contact	Causes severe skin burns.

2-Butoxy ethanol may be absorbed through the skin in toxic amounts if contact is repeated and prolonged. These effects have not been observed in humans.

Prolonged or repeated exposure may cause liver and kidney damage. These effects have not been observed in humans.

Eye contact Causes serious eye damage.

Symptoms related to the physical, chemical and toxicological characteristics Burning pain and severe corrosive skin damage. Causes serious eye damage. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Permanent eye damage including blindness could result. May cause respiratory irritation.

Information on toxicological effects

Acute toxicity In high concentrations, vapors are anesthetic and may cause headache, fatigue, dizziness and central nervous system effects. Harmful if inhaled. Harmful if swallowed. May cause respiratory irritation.

Product	Species	Test Results
Superscope II (CAS Mixture)		
Acute		
<i>Dermal</i>		
LD50	Rabbit	7829.5825 mg/kg estimated

Product	Species	Test Results
<i>Inhalation</i>		
LC50	Mouse	17266.8965 ppm, 7 Hours estimated
	Rat	11100.1484 ppm, 4 Hours estimated
<i>Oral</i>		
LD50	Mouse	9413.3379 mg/kg estimated
	Rat	5002.291 mg/kg estimated

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Causes severe skin burns and eye damage.
Serious eye damage/eye irritation	Causes serious eye damage.
Respiratory or skin sensitization	
Respiratory sensitization	Not available.
Skin sensitization	This product is not expected to cause skin sensitization.
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
IARC Monographs. Overall Evaluation of Carcinogenicity	
BUTOXYETHANOL (CAS 111-76-2)	3 Not classifiable as to carcinogenicity to humans.
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)	
Not listed.	
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	May cause respiratory irritation.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Not available.
Chronic effects	Prolonged inhalation may be harmful. May be harmful if absorbed through skin. 2-Butoxy ethanol may be absorbed through the skin in toxic amounts if contact is repeated and prolonged. These effects have not been observed in humans. Prolonged or repeated exposure may cause liver and kidney damage. These effects have not been observed in humans.

12. Ecological information

Ecotoxicity	Toxic to aquatic life with long lasting effects. Accumulation in aquatic organisms is expected.		
Product	Species		
Test Results			
Superscope II (CAS Mixture)			
Aquatic			
Crustacea	EC50	Daphnia	377.9316 mg/l, 48 hours estimated
Fish	LC50	Fish	1546.9042 mg/l, 96 hours estimated

* Estimates for product may be based on additional component data not shown.

Persistence and degradability	No data is available on the degradability of this product.		
Bioaccumulative potential	No data available.		
Partition coefficient n-octanol / water (log Kow)			
2-AMINOETHANOL		-1.31	
BUTOXYETHANOL		0.83	
ETHYLENE GLYCOL PHENYL ETHER		1.16	
Mobility in soil	No data available.		
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.		

13. Disposal considerations

Disposal instructions	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international regulations.
Local disposal regulations	Dispose in accordance with all applicable regulations.
Hazardous waste code	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT	
UN number	UN3266
UN proper shipping name	Corrosive liquid, basic, inorganic, n.o.s. (POTASSIUM HYDROXIDE RQ = 36275 LBS), MARINE POLLUTANT
Transport hazard class(es)	
Class	8
Subsidiary risk	-
Label(s)	8
Packing group	III
Environmental hazards	
Marine pollutant	Yes
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Special provisions	A6, T14, TP2, TP27
Packaging exceptions	None
Packaging non bulk	201
Packaging bulk	243
IATA	
UN number	UN3266
UN proper shipping name	Corrosive liquid, basic, inorganic, n.o.s. (POTASSIUM HYDROXIDE)
Transport hazard class(es)	
Class	8
Subsidiary risk	-
Packing group	III
Environmental hazards	Yes
ERG Code	8L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Other information	
Passenger and cargo aircraft	Allowed.
Cargo aircraft only	Allowed.
IMDG	
UN number	UN3266
UN proper shipping name	CORROSIVE LIQUID, BASIC, INORGANIC, N.O.S. (POTASSIUM HYDROXIDE), MARINE POLLUTANT
Transport hazard class(es)	
Class	8
Subsidiary risk	-
Packing group	III
Environmental hazards	
Marine pollutant	Yes
EmS	F-A, S-B
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

This substance/mixture is not intended to be transported in bulk.

DOT



IATA; IMDG



Marine pollutant



General information

DOT Regulated Marine Pollutant. IMDG Regulated Marine Pollutant.

15. Regulatory information

US federal regulations

This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
All components are on the U.S. EPA TSCA Inventory List.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

BUTOXYETHANOL (CAS 111-76-2)	Listed.
ETHYLENE GLYCOL PHENYL ETHER (CAS 122-99-6)	Listed.
POTASSIUM HYDROXIDE (CAS 1310-58-3)	Listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories

Immediate Hazard - Yes
Delayed Hazard - No
Fire Hazard - No
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes**SARA 313 (TRI reporting)**

Chemical name	CAS number	% by wt.
BUTOXYETHANOL	111-76-2	3 - < 5
ETHYLENE GLYCOL PHENYL ETHER	122-99-6	1 - < 3

Other federal regulations**Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List**

ETHYLENE GLYCOL PHENYL ETHER (CAS 122-99-6)

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.**US state regulations****US. Massachusetts RTK - Substance List**

2-AMINOETHANOL (CAS 141-43-5)
 BUTOXYETHANOL (CAS 111-76-2)
 POTASSIUM HYDROXIDE (CAS 1310-58-3)

US. New Jersey Worker and Community Right-to-Know Act

2-AMINOETHANOL (CAS 141-43-5)
 BUTOXYETHANOL (CAS 111-76-2)
 ETHYLENE GLYCOL PHENYL ETHER (CAS 122-99-6)
 POTASSIUM HYDROXIDE (CAS 1310-58-3)

US. Pennsylvania Worker and Community Right-to-Know Law

2-AMINOETHANOL (CAS 141-43-5)
 BUTOXYETHANOL (CAS 111-76-2)
 ETHYLENE GLYCOL PHENYL ETHER (CAS 122-99-6)
 POTASSIUM HYDROXIDE (CAS 1310-58-3)

US. Rhode Island RTK

BUTOXYETHANOL (CAS 111-76-2)
 ETHYLENE GLYCOL PHENYL ETHER (CAS 122-99-6)
 POTASSIUM HYDROXIDE (CAS 1310-58-3)

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

16. Other information, including date of preparation or last revision

Issue date 09-04-2014
Revision date 04-24-2015
Version # 02

Disclaimer The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

Revision Information Product and Company Identification: Alternate Trade Names
 Physical & Chemical Properties: Multiple Properties
 Toxicological Information: Toxicological Data
 Transport Information: Material Transportation Information
 HazReg Data: North America
 GHS: Classification