



Pony Testing International Group

Report No.: MDI8BSFN79892716

# SDS Report

Sample Description  
& Model

Li-polymer Battery PT505068

Applicant

Shenzhen Pow-Tech New Power Co., Ltd.

Address

1204, Tower 3, Zhuoyue Meilin Center Square,  
Futian District, Shenzhen

No.: MDI8BSFN79892716  
Code: n4t1n8ua



**PONY 谱尼测试**  
Pony Testing International Group

www.ponytest.com

☎Hotline 400-819-5688

北京实验室: (010) 82618116 长春实验室: (0431) 85150908 上海实验室: (021) 64851999 深圳实验室: (0755) 26050909  
青岛实验室: (0532) 88706866 大连实验室: (0411) 84650820 宁波实验室: (0574) 87736499 广州实验室: (020) 89224310  
天津实验室: (022) 27360730 郑州实验室: (0371) 69350670 杭州实验室: (0571) 87219096 武汉实验室: (027) 83997127





## Safety Data Sheet

According to ST/SG/AC.10/30/Rev.6 (GHS)

### Section 1 - Chemical Product and Company Identification

#### Chemical product identification

**Sample Description:** Li-polymer Battery

**Sample Model:** PT505068

**Recommended Uses:** N/A

**Restrictions on use:** N/A

**Supplier name:** Shenzhen Pow-Tech New Power Co., Ltd.

**Address:** 1204, Tower 3, Zhuoyue Meilin Center Square, Futian District, Shenzhen

**Phone number:** 0755-82721259/82721159

**FAX:** 0755-82721250

**E-mail:** luisa-wang@szpowtech.com.cn

**Emergency phone number:** 0755-82721259

### Section 2 - Hazards Identification

**Emergency overview:** This product is an article which contains a chemical substance. Safety information is given for exposure to the article as sold. Intended use of the product should not result in exposure to the chemical substance. This is a battery.

In case of rupture: the below hazards exist.

**CAS#** 7429-90-5

#### Classification according to GHS

Specific target organ toxicity, repeated exposure (1) (Lung)

Hazardous to the aquatic environment, long-term hazard (4)

#### Label elements

**Hazard pictogram(s):**



**Signal word:** Danger

**Hazard statement(s):**

H372 Causes damage to organs through prolonged or repeated exposure (Lung)

H413 May cause long lasting harmful effects to aquatic life

**Precautionary statement(s):**

www.ponytest.com ©Hotline 400-819-5688



**Prevention:**

- P260 Do not breathe dust.
- P264 Wash skin and clothing thoroughly after handling.
- P270 Do not eat, drink or smoke when using this product.
- P273 Avoid release to the environment.

**Response:**

- P314 Get medical advice if you feel unwell.

**Storage**

None.

**Disposal:**

- P501 Contents handling to approved waste treatment plants.

**CAS# 7440-50-8**

**Classification according to GHS**

- Specific target organ toxicity, single exposure; Respiratory tract irritation (3)
- Specific target organ toxicity, repeated exposure (1) (liver)
- Hazardous to the aquatic environment, long-term hazard (3)

**Label elements**

**Hazard pictogram(s):**



**Signal word:**

Danger

**Hazard statement(s):**

- H335 May cause respiratory irritation
- H372 Causes damage to organs through prolonged or repeated exposure (liver)
- H412 Harmful to aquatic life with long lasting effects

**Precautionary statement(s):**

**Prevention:**

- P271 Use only outdoors or in a well-ventilated area.
- P260 Do not breathe dust.
- P264 Wash skin and clothing thoroughly after handling.
- P270 Do not eat, drink or smoke when using this product.
- P273 Avoid release to the environment.

**Response:**

- P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
- P312 Call a POISON CENTER or doctor, if you feel unwell.

**Storage**

- P403 + P233 Store in a well-ventilated place. Keep container tightly closed.

www.ponytest.com ©Hotline 400-819-5688



**Disposal:**

P501 Contents or container handling to approved waste treatment plants.

**Other hazards**

**Physical and chemical hazards:** See Section 10

**Human health hazards:** See Section 11

**Environmental hazards:** See Section 12

### Section 3 – Composition/Information on Ingredients

**Chemical characterization: Mixture**

Chemical Composition	CAS No.	EC#	Weight (%)
Cobaltate, lithium	12190-79-3	235-362-0	33.5
Aluminium	7429-90-5	231-072-3	9
Graphite	7782-42-5	231-955-3	18
Copper	7440-50-8	231-159-6	15
Phosphate(1-), hexafluoro-, lithium	21324-40-3	244-334-7	15.5
Other	---	---	9

### Section 4 - First Aid Measures

**Description of first aid measures**

**General information** No special measures required.

**After eye contact**

Flush eyes with plenty of water for several minutes while holding eyelids open. Get medical attention if irritation persists.

**After skin contact**

Remove contaminated clothing and shoes. Immediately wash with water and soap and rinse thoroughly. Wash clothing and shoes before reuse. If irritation occurs, get medical attention.

**After inhalation**

Remove victim to fresh area. Administer artificial respiration if breathing is difficult. Seek medical attention.

**After swallowing**

Do not induce vomiting. Get medical attention.

www.ponytest.com      ☎Hotline 400-819-5688

北京实验室: (010) 82618116    长春实验室: (0431) 85150908    上海实验室: (021) 64851999    深圳实验室: (0755) 26050909  
 青岛实验室: (0532) 88706866    哈尔滨实验室: (0451) 88104561    宁波实验室: (0574) 87736499    广州实验室: (020) 89224310  
 天津实验室: (022) 27360730    大连实验室: (0411) 84650820    杭州实验室: (0571) 87219096    武汉实验室: (027) 83997127  
 新疆实验室: (0991) 6684186    郑州实验室: (0371) 69350670    苏州实验室: (0512) 62997900    厦门实验室: (0592) 5568048





**Personal protective equipment for first-aid responders:** No data available.

**Most important symptoms/effects, acute and delayed:** No data available.

**Indication of immediate medical attention and special treatment needed:** No data available.

## Section 5 - Fire Fighting Measures

### Suitable extinguishing media:

Use extinguishing agent suitable for local conditions and the surrounding environment .  
Such as dry powder , CO<sub>2</sub>.

### Unsuitable extinguishing media:

No data available.

### Specific Hazards arising from the chemical:

Special hazards arising from the substance or mixture

Battery may burst and release hazardous decomposition products when exposed to a fire situation. Lithium ion batteries contain flammable electrolyte that may vent, ignite and produce sparks when subjected to high temperature(>150°C(302°F)), when damaged or abused (e.g. mechanical damage or electrical overcharging); may burn rapidly with flare-burning effect; may ignite other batteries in clothes proximity.

### Specific protective actions for fire-fighters:

Protective equipment: Wear self-contained respirator. Wear fully protective impervious suit.

## Section 6 - Accidental Release Measures

### Personal precautions:

Wear protective equipment. Keep unprotected persons away. Ensure adequate ventilation

### Protective equipment:

No data available.

### Emergency procedures:

Remove ignition sources, evacuate area. Sweep up using a method that does not generate dust. Collect as much of the spilled material as possible, placed the spilled material into a suitable disposal container. Keep spilled material out of sewers, ditches and bodies of water.

### Environmental precautions:

Do not allow material to be released to the environment without proper governmental permits.

### Methods and materials for containment and cleaning up:

All waste must refer to the United Nations, the national and local regulations for disposal.





See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

## Section 7 - Handling and Storage

### Precautions for safe handling:

Consumption of food and beverage should be avoided in work areas.

Wash hands with soap and water before eating, drinking.

Ground containers when transferring liquid to prevent static accumulation and discharge.

### Information about fire and explosion protection

Batteries may explode or cause burns, if disassembled, crushed or exposed to fire or high temperatures. Do not short or install with incorrect polarity.

### Conditions for safe storage, including any incompatibilities:

#### Requirements to be met by storerooms and receptacles

Store in a cool, dry, well-ventilated place.

#### Information about storage in one common storage facility

Keep away from heat, avoiding the long time of sunlight.

#### Further information about storage conditions

Keep container tightly sealed.

#### Specific and use

No data available.

## Section 8 - Exposure Controls/Personal Protection

### Control parameters

CAS No.	ACGIH	NIOSH	OSHA
12190-79-3	N/A	N/A	N/A
7429-90-5	TLV-TWA 10mg/m <sup>3</sup> TLV-TWA 5mg/m <sup>3</sup>	REL-TWA 2mg/m <sup>3</sup> REL-TWA 5mg/m <sup>3</sup> REL-TWA 10mg/m <sup>3</sup>	PEL-TWA 5mg/m <sup>3</sup> PEL-TWA 15mg/m <sup>3</sup>
7782-42-5	TLV-TWA 2mg/m <sup>3</sup>	REL-TWA 2.5mg/m <sup>3</sup>	PEL-TWA 15mppcf PEL-TWA 20mppcf
7440-50-8	TLV-TWA 0.2mg/m <sup>3</sup> TLV-TWA 1mg/m <sup>3</sup>	REL-TWA 1mg/m <sup>3</sup> REL-TWA 0.1mg/m <sup>3</sup>	PEL-TWA 0.1mg/m <sup>3</sup> PEL-TWA 1mg/m <sup>3</sup>
21324-40-3	N/A	N/A	N/A





#### Appropriate engineering controls:

The usual precautionary measures for handling chemicals should be followed.

Keep away from foodstuffs, beverages and feed.

Remove all soiled and contaminated clothing immediately.

Wash hands before breaks and at the end of work.

#### Personal Protective Equipment

**Respiratory protection:** Wear suitable protective mask in order to reduce the respiratory system. A large number of leakage, wear chemical protective clothing, including self-contained breathing apparatus.

**Hand Protection:** Wear appropriate protective gloves to reduce skin contact.

**Eyes Protection:** Wear safety goggles or eye protection combined with respiratory protection.

**Skin and Body Protection:** Working environment required, wear suitable protective clothing to minimize contact with skin. The type of protective equipment must be according to the concentration and the content of certain hazardous substances in the workplace.

## Section 9 - Physical and Chemical Properties

#### Information on basic physical and chemical properties

Colour:	Silver.
Physical State:	Prismatic.
Odour:	Not available.
Odour threshold:	Not available.
pH:	Not available.
Melting point/freezing point:	Not available.
Initial boiling point and boiling range:	Not available.
Flash Point:	Not available.
Evaporation rate:	Not available.
Flammability (solid, gas):	Not available.
Explosion Limits (vol% in air):	Not available.
Vapour pressure, kPa at 20°C:	Not available.
Vapor density:	Not available.
Density/Relative density (water = 1):	Not available.





<b>Solubility(ies):</b>	Not available.
<b>Partition coefficient: n-octanol/water:</b>	Not available.
<b>Auto-ignition temperature:</b>	Not available.
<b>Decomposition temperature:</b>	Not available.
<b>Viscosity:</b>	Not available.
<b>Other information:</b>	
<b>Voltage</b>	3.7V
<b>Electric capacity</b>	2000mAh
<b>Electric Energy</b>	7.4Wh

### Section 10 - Stability and Reactivity

**Reactivity:** No data available.

**Chemical stability:** Stable.

**Possibility of hazardous reactions:** No data available.

**Conditions to Avoid:** Flames, sparks, and other sources of ignition, incompatible materials.

**Incompatibilities materials:** Oxidizing agents, acid, base.

**Hazardous decomposition products:** Carbon monoxide, carbon dioxide, lithium oxide fumes.

### Section 11 - Toxicological Information

**Acute Toxicity:**

CAS No.	LC50/LD50
12190-79-3	No data available.
7429-90-5	No data available.
7782-42-5	No data available.
7440-50-8	No data available.
21324-40-3	No data available.

**Skin corrosion/irritation:** No data available.

**Serious eye damage/irritation:** No data available.

**Respiratory or Skin sensitization:** No data available.

**Germ Cell mutagenicity:** No data available.

**Carcinogenicity:** No data available.

**Reproductive toxicity:** No data available.





**Specific target organ toxicity-Single exposure:** No data available.

**Specific target organ toxicity-Repeated exposure:** No data available.

**Aspiration hazard:** No data available.

**Information on the likely routes of exposure:** No data available.

**Eye:** No data available.

**Skin:** No data available.

**Ingestion:** No data available.

**Inhalation:** No data available.

## Section 12 - Ecological Information

**Ecological Toxicity:** No data available.

**Persistence and degradability:** No data available.

**Bioaccumulative Potential:** No data available.

**Mobility in Soil:** No data available.

**Other adverse effects:** No data available.

## Section 13 - Disposal Considerations

**Disposal methods:**

**Recommendation:**

Consult state, local or national regulations to ensure proper disposal.

**Uncleaned packaging**

**Recommendation:** Disposal must be made according to official regulations.

## Section 14 - Transport Information

According to the Packing Instruction 965~967 of IATA DGR 57<sup>th</sup> Edition for transportation, or the special provision 188 of IMDG (37-14), or the <<Recommendations On The Transport Of Dangerous Goods-Model Regulations>> (19<sup>th</sup>).

**Transport Fashion:** By air, by sea, by railway, by road.

## Section 15 - Regulatory Information

**Safety, health and environmental regulations/legislation specific for the substance or mixture**

www.ponytest.com ©Hotline 400-819-5688

北京实验室: (010) 82618116	长春实验室: (0431) 85150908	上海实验室: (021) 64851999	深圳实验室: (0755) 26050909
青岛实验室: (0532) 88706866	哈尔滨实验室: (0451) 88104561	宁波实验室: (0574) 87736499	广州实验室: (020) 89224310
天津实验室: (022) 27360730	大连实验室: (0411) 84650820	杭州实验室: (0571) 87219096	武汉实验室: (027) 83997127
新疆实验室: (0991) 6684186	郑州实验室: (0371) 69350670	苏州实验室: (0512) 62997900	厦门实验室: (0592) 5568048





CAS No.	TSCA	IECSC	DSL/NDSL	EINECS/ ELINCS/ NLP
12190-79-3	Listed	Listed	Listed DSL	Listed
7429-90-5	Listed	Listed	Listed DSL	Listed
7782-42-5	Listed	Listed	Listed DSL	Listed
7440-50-8	Listed	Listed	Listed DSL	Listed
21324-40-3	Listed	Listed	Listed DSL	Listed

## Section 16 - Other Information

Issue Time: 2016-05-30

Issue Department: Technical department

Modification record:

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

Other Information:

CAS: (Chemical Abstracts Service);

EC: (European Commission);

ACGIH: (American Conference of Governmental Industrial Hygienists);

NIOSH: (US National Institute for Occupational Safety and Health);

OSHA: (US Occupational Safety and Health);

TLV: (Threshold Limit Value)

TWA: (Time Weighted Average);

STEL: (Short Term Exposure Limit);

PEL: (Permissible Exposure Level);

REL: (Recommended Exposure Limit);

PC-STEL: (Permissible concentration-time weighted average);

PC-TWA: (Permissible concentration-short time exposure limit);

LC50: (Lethal concentration, 50 percent kill);

LD50: (Lethal dose, 50 percent kill);

IARC: (International Agency for Research on Cancer);

EC50: (Median effective concentration);

BCF: (Bioconcentration Factor);

www.ponytest.com ☎Hotline 400-819-5688





BOD: (Biochemical oxygen demand);  
 NOEC: (No observed effect concentration);  
 NTP: (US National Toxicology Program);  
 RTECS: (Registry of Toxic Effects of Chemical Substances);  
 IATA: (International Air Transport Association);  
 IMDG: (International Maritime Dangerous Goods);  
 TDG: (Recommendations on the TRANSPORT OF DANGEROUS GOODS Model Regulations);  
 TOC: (Total Organic Carbon);  
 TSCA: (Toxic Substances Control Act of USA);  
 DSL: (the Domestic Substances List of Canada);  
 NDSL: (the Non-domestic Substances List of Canada)

\*\*\*End of report\*\*\*