

FDLTMAG2

EnOcean® Enabled Wireless Solar Door / Window Sensor, 902 MHz

WIRELESS SOLAR DOOR / WINDOW TRANSMITTER

Specifications

Minimum Illumination:	400 lux hours per day e.g. 100 lux for 4 hours or 200 lux for 2 hours
Start-up Time:	Less than 2.5 min @ 400 lux
Operating Life in Darkness (after full charge):	Min 10 days signs-of-life only
Operating Life in Darkness (with backup battery):	Min 5 years
Maximum Sensor Gap:	0.16" (4mm)
Dimensions (Sensor):	3.00" L x 0.87" W x 0.59" D (76mm x 22mm x 15mm)
Dimensions (with mounting plate):	3.15" L x 0.47" W x 0.50" D (80mm x 12mm x 13mm)
Drill Distance:	2.05" (52mm)
Environment:	Indoor use only -4 to 140 F (-20 to 60 C) 5 to 93% relative humidity (noncondensing)
Agency Compliance:	FCC ID: SZV-STM 320U IC: 5713A-STM 320U



Notes:

- Typical range: 100 ft.
 - Open area transmission could be farther. Consult factory for more information.
- For use with FDLR Series Relays.
- EEP D5-00-01