



Functional Devices, Inc. 101 Commerce Drive Sharpsville, IN 46068 Toll Free: (800) 888-5538 Office: (765) 883-5538 Fax: (765) 883-7505 Email: sales@functionaldevices.com Website: www.functionaldevices.com

LRL24BM

Enclosed Mechanically Latching Relay 20 Amp SPST with 24 Vac/dc Coil, Status LED and Auxiliary Output



LATCHING RELAY



SPECIFICATIONS

Relays & Contact Type: One (1) SPST Latching Relay, Dual Coil Expected Relay Life: 1 million cycles minimum mechanical

Operating Temperature: -30 to 140° F

Humidity Range: 5 to 95% (noncondensing)

Operate Time: 50ms

Maximum Pulse Length: 30 seconds

Relay Status / Auxiliary

Contact Closed: LED On = Voltage Detected on Load Wire Dimensions: 2.30" x 3.20" x 1.80" with .50" NPT Nipple

Wires: 16", 600V Rated

Approvals: UL Listed, UL60947, C-UL, CE, RoHS **Housing Rating:** UL Accepted for Use in Plenum, NEMA 1

Gold Flash: No Override Switch: No

Contact Ratings:

20 Amp Resistive @ 120-277 Vac 20 Amp Ballast @ 120-277 Vac 16 Amp Electronic Ballast @ 120-277 Vac 5540 Watt Tungsten @ 277 Vac 720 VA Pilot Duty @ 120-277 Vac 2 HP @ 277 Vac 3 HP @ 240 Vac

3 HP @ 240 Vac 1.5 HP @ 120 Vac

Coil Current:

175 mA @ 20 Vac 210 mA @ 24 Vac 92 mA @ 20 Vdc 110 mA @ 24 Vdc 138 mA @ 30 Vdc

Latch / Unlatch:

Min. 20 Vdc / 22 Vac

Auxiliary Contact:

3 Amp @ 30 Vac/dc max.

Notes:

- Application of momentary voltage on latch coil (Wht/Blu & Wht/Yel) will close the contact.
- Application of momentary voltage on unlatch coil (Wht/Red & Wht/Yel) will open the contact.
- Auxiliary contact and status LED activate when 120-277 Vac is applied between Load (Org) wire and Load Neutral (Wht/Blk) wire.