

Product data sheet

Characteristics

QO112L125PGC

Load center, QO, 1 phase, 12 spaces, 24 circuits, 125A convertible main lugs, PoN, NEMA1, gnd bar, combo cover, UL



Main

Marketing Trade Name	QO
Product Type	Load Center
Cover Type	Combination flush/surface cover
Provided Equipment	Grounding bar Cover

Complementary

Tightening Torque	Cover: 20 lb.in
Load Center Type	Main lugs
Rated Current	125 A
Number of Spaces	12
Max Short Circuit Current Rating	65 kA
Maximum Number of Single Pole Circuits	24
Maximum Number of Tandem Breakers	12
Number of Phases	1 phase
Ground Bar	Grounding bar included (not installed)
Box Number	6
Height	17.92 in (455.17 mm)
Width	14.25 in (361.95 mm)
Depth	3.75 in (95.25 mm)

Environment

Enclosure Rating	NEMA 1 for indoor
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed


Ordering and shipping details

Category	10003 - QO PON 1PH LC,12-60 CKT, ML N1
Discount Schedule	DE3A
GTIN	00785901590422
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability


California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Approximate Dimensions




KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64


Connections and Wiring Diagrams




QO112L125PG
QO112L125PGC



QO116M100P
QO116M100PC



QO120M100P
QO120M100PC



QO120L125PG
QO120L125PGC