

HONEYWELL UVEX A700 SERIES

The lightweight wraparound 9-base lens design provides substantial coverage and a distortion-free 180° field of vision, while the universal nose bridge and soft temple tips provide a comfortable fit. Available in a wide selection of tints to meet a variety of indoor and outdoor work applications. Clear and Gray lens options are available with Uvextra® Fog-Resistant coating for humid conditions.



FEATURES AND BENEFITS

- · Sport-inspired shaping provides a stylish fit for the everyday worker
- · Lightweight, flexible temples with padded tips provide a secure, wraparound fit and all-day comfort
- Molded universal nose bridge provides a comfortable fit
- 9-base polycarbonate hardcoated lens provides a 180° field of distortion-free vision
- Provides >99.9% UV protection
- Meets ANSI Z87.1 and is CSA Z94.3 certified

HONEYWELL UVEX® A700 ORDERING INFORMATION

SKU	FRAME COLOR	LENS COLOR	LENS COATING
A700	Clear	Clear	Anti-scratch Hardcoat
A701	Gray	Gray	Anti-scratch Hardcoat
A703	Gray	Blue Mirror	Anti-scratch Hardcoat
A704	Gray	Silver Mirror	Anti-scratch Hardcoat
A705	Clear	Clear	Uvextra® Fog Resistant coating
A706	Gray	Gray	Uvextra® Fog Resistant coating

Packaging Information:

• Polybag, 10/stocker, 200/case

• Unit size: 5" x 9"

• Unit weight: .75 oz.

• Stocker size: 11.25" x 6.875" x 4"

• Stocker weight: 14.5 oz.

• Case size: 23.25" x 20.75" x 15.75"

• Case weight: 27.5 lbs.

For more information

sps.honeywell.com

Technical Service: 800.873.5242

Honeywell Personal Protective Equipment (PPE)

855 S Mint St Charlotte, NC 28202

JS: Canada:

Tel. 800.430.5490 Tel. 888.212.7233 Fax. 800.322.1330 Fax. 888.667.8477

