

## Product data sheet

### Characteristics

# QU12L400CL

Meter mains, QO, combination service entrance, ringless socket, 400A, surface mount, maximum 12 spaces, class 320, lever bypass



### Main

Product or component type	Meter Mains
Range of product	QO
Includes	Fifth jaw

### Complementary

Line Rated Current	400 A
Short-circuit current	25 kA
Network number of phases	1
Meter socket type	Ringless
Mounting	Surface Semi flush field installed flange kit
Number of spaces	12
Number of circuits	0
Number of Tandem Breakers	0
Hub type	A-L
Electrical connection	Lugs service ground Studs line side
Wire Size	AWG 4...250 kcmil aluminium)service ground AWG 4...250 kcmil copper)service ground
Disconnect	Service disconnect (factory installed) Service disconnect (ordered separately)
Main Breaker Rating	200 A
Service feed location	UG
Bypass type	Class 320 lever bypass
Height	43.00 in (1092.20 mm)
Width	28.25 in (717.55 mm)
Depth	7.87 in (199.90 mm)

### Environment

Product certifications	UL E-6294
------------------------	-----------

### Ordering and shipping details

Category	00022 - QO METER MAINS
Discount Schedule	DE3A
GTIN	00785901421009
Nbr. of units in pkg.	1
Package weight(Lbs)	112 lb(US) (50.80 kg)

Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	0.80 ft (0.244 m)
Package 1 width	2.44 ft (0.744 m)
Package 1 Length	3.52 ft (1.074 m)

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------