



Main

Product Type	Circuit Breaker Retaining Kit
Marketing Trade Name	Homeline



Complementary

Rated Current	100...125 A
Height	4.4 in (111.76 mm)
Width	5.07 in (128.78 mm)
Depth	3.05 in (77.47 mm)
Tightening Torque	4 N.m

Ordering and shipping details

Category	00185 - MISC. HOM LOAD CENTERS
Discount Schedule	DE3C
GTIN	00785901307204
Nbr. of units in pkg.	10
Package weight(Lbs)	0.15 lb(US) (0.07 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.90 in (4.826 cm)
Package 1 width	4.00 in (10.16 cm)
Package 1 Length	4.90 in (12.446 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Weight	31.20 oz (884.504 g)
Package 2 Height	7.10 in (18.034 cm)
Package 2 width	7.30 in (18.542 cm)
Package 2 Length	8.00 in (20.32 cm)
Unit Type of Package 3	PAL
Number of Units in Package 3	750
Package 3 Weight	143.00 lb(US) (64.864 kg)
Package 3 Height	40.00 in (101.6 cm)
Package 3 width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------