



Main

Product	Double Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Number of Poles	3
Current Rating	200 A
Voltage Rating	480 V AC 250 V DC
Enclosure Rating	NEMA 1
Maximum Horse Power Rating	15 hp 480 V at AC 50-60 Hz for 3 phase conforming to NEC 430.52

Complementary

Short-circuit current	10 kA H or J
Fuse type	H or J
Mounting Type	Surface
Wire Size	AWG 6...300 kcmil copper or aluminium
Tightening torque	340 lbf.in (38.41 N.m) (AWG 6...300 kcmil)
Depth	10.63 in (270.00 mm)
Width	26.25 in (666.75 mm)
Height	32.5 in (825.50 mm)
Net Weight	136.69 lb(US) (62 kg)

Environment

Certifications	UL Listed
----------------	-----------

Ordering and shipping details

Category	00134 - DT SWITCH,NEMA12
Discount Schedule	DE1
GTIN	00785901077077
Nbr. of units in pkg.	1
Package weight(Lbs)	143 lb(US) (64.86 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REAcH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------
