

NRL Series 4K H.265 NVR A Lite Smart NVR with PoE

N4NRL

4 Channel NVR with 4 Built-In PoE Ports

N8NRL

8 Channel NVR with 8 Built-In PoE Ports

STORAGE <u> 1TB - 8TB</u>

N4NRL1TB	N4NRL4TB	N8NRL1TB	N8NRL4TB
N4NRL2TB	N4NRL6TB	N8NRL2TB	N8NRL6TB
N4NRL3TB	N4NRL8TB	N8NRL3TB	N8NRL8TB


















Front panel







Key Features

EZ Wizards - For ease of use and setup

Camera: quickly discover and install all Speco IP cameras

Setup: for quick setup of general settings

Network: network setup and port forwarding

Record: quickly setup recording resolutions and recording type

Search: quickly search for events from thumbnails

Copy: quickly copy what you are playing onto a USB flash drive

- Real time recording up to 8MP resolution (4K) at 30fps
- H.265 compression Store up to 2x more than H.264!
- Built-in PoE ports for all channels for easy installation
- 1 SATA port for up to 8TB of storage
- 4K HDMI out and VGA monitor output
- Object and line crossing detection and alerts*
- Smart Search Specify a region on the camera view and search on changes in that area*
- 2-way audio communication
- Free US-based DDNS and P2P services
- Remote viewing via web browser or your mobile device
- Easy video exporting via USB
- 5 year limited warranty¹

*with Speco Smart Analytic Cameras

Optional Accessory **ERS1V** Vented Rack Shelf

Additional Features

- Plug & play feature with isolated traffic on the PoE ports with Speco's IP cameras
- Find and install IP cameras on the local network without needing to locate the cameras manually
- Supports different recording types: Continuous, Motion, Analytics, and Sensor
- Create bookmark pins on playback for easy reference
- Instant playback for individual channels directly from the live view screen
- Customizable channel view placement
- Remote monitoring, recording, playback, configuration, upgrades, and PTZ control via the internet
- Simultaneous HDMI & VGA video output
- Built-in S.M.A.R.T technology (Self-Monitoring, Analysis and Reporting Technology for HDD)
- Supports 2-way audio communication (speaker required)
- Works with a majority of cameras that are conformant with ONVIF Profile S

Limited Warranty/Hard drives excluded. Check www.specotech.com for more details. iPhone is a trademark of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc.The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 9/11/18













Model		NRL			
Video		Max. IP Channels	4	8	
	Input	IP Camera	H.264/H.265 Auto	Detection (Max 8MP)	
		Main Monitor	HDMI (Max. 4K) and VGA (Max. Full HD)		
	Output	Sub Monitor	n/a		
		Local Input/Output	0/1		
Audio					
Audio	Codec		G.711A/G.711U		
	Audio Input		1ch, RCA, 4CH IPC input 1ch, RCA, 8CH IPC input		
_	E	ncoding Resolutions	8MP/5MP/4MP/3MP/1080P/720P		
Recording	Codec		H.264/H.265 (Auto Detection)		
	Max Frame Rate per Channel		Any Resolution @30fps		
	Recording Mode		Analytics/Continuous/Motion/Sensor/Schedule/Manual		
	Pre-Recording		Max. 5 seconds		
	Post Recording		Max. 10 minutes		
		Search	EZ Search, Motion, Specific Date/Time, Event, Museum, Bookmarks, Snapshots, Log		
Search		Multi-Decoding	1, 4	1, 4, 8	
& Playback	P	layback Resolutions	8MP/5MP/4MP/3MP/1080P/720P		
ayzaek		Playback Functions	Play, pause, FF, FB, digital zoom, etc.		
	Media		USB drive, USB Portable HDD, Network		
Backup			JPG, AVI, ZIP (Player+Proprietary Data)		
		Capacity of 1 HDD	8TB		
	HDD				
Storage	USB Internal HDDSs Front Rear		1		
			1		
	Input/Output		n/a		
Alarm	Trigger Events		Recording, PTZ, Alarm Out, Pop-up alarm preview, Email, FTP, Snapshot, Buzzer and Screen Tips		
User I/F	Input Method			IR Remote, Mouse	
0301 1/ 1	Port		100Mbps + 4PoE	100Mbps + 8PoE	
Network			'		
Network	P2P/Dynamic DNS		Free US-Based Speco P2P and DDNS Service		
		Network Protocols	TCP/IP, PPPoE, DHCP, DNS, UPnP, NTP, SMTP		
		Mobile	iOS/Android via Speco Blue App		
Network		Web Viewer	Windows IE		
Access		VMS	SecureGuard®		
	Max. User Access		Max 10 users online (web client)		
		Digital Zoom	Live and Playback, Free Size		
Features	Smart Analysis		Abandoned object detection, Missing object detection, Line Crossing ONVIF 2.3		
	ONVIF Support S.M.A.R.T		ONVIF 2.3 Temperature, Power On Time, Bad Sectors and Health		
Power	Input Voltage		DC48V		
	Power Consumption		≤ 5W (wuthout HDD)	≤ 15W (without HDD)	
Environment					
	Operating Temperature		-10°C ~ 50°C		
	Operating Humidity		10% ~ 90% humidity (Non-condensing)		
Dimensions	Unit		300mm x 248mm x 52mm (11.8" x 9.8" x 2.0")		







