


VLSFH1UL

Disconnect switch, TeSys VLS, CC fuse holder, for 3 pole disconnect switch, for up to 25A fuse



Main

Range	TeSys
Product name	TeSys VARIO LS
Device short name	VLSFH
Fuse size	CC
Product or component type	Fuse holder
Poles description	3P
Network type	AC

Complementary

Network frequency	50/60 Hz
Mounting support	DIN rail
[Ui] rated insulation voltage	690 V AC 50/60 Hz
[Ith] conventional free air thermal current	25 A 131 °F (55 °C)
Connections - terminals	Power circuit screw clamp terminals 0.02 in ² (10 mm ²) solid Power circuit screw clamp terminals 0.02 in ² (16 mm ²) flexible without cable end
Tightening torque	Power circuit 15.93...17.70 lbf.in (1.8...2 N.m) screw clamp terminals
Height	2.96 in (75.2 mm)
Width	2.07 in (52.5 mm)
Depth	3.15 in (80.1 mm)
Net Weight	0.30 lb(US) (0.135 kg)

Environment

Standards	UL 508 CSA C22.2 No 14 IEC 60947-3
Product certifications	CULus GL
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-13...131 °F (-25...55 °C)

Ordering and shipping details

Category	21734 - TESYS VLS DISCONNECT SWITCHES
Discount Schedule	CP1
GTIN	00785901575887
Nbr. of units in pkg.	1
Package weight(Lbs)	0.29 lb(US) (0.13 kg)
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.56 in (6.5 cm)
Package 1 width	3.54 in (9 cm)
Package 1 Length	3.82 in (9.7 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	18
Package 2 Weight	6.05 lb(US) (2.746 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration