

Product data sheet

Characteristics

8940XD4S2V06H30

Pump Panel, NEMA Type S, Well Guard, oil field, Size 2, 45A, 25 HP, HLL36050M72 circuit breaker, Motor Logic SSOLR, 480 VAC 60 Hz coil, NEMA 3R



Main

Product	Well-Guard Control
Type	S2
Device application	Pumping

Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	45 A
Number of Poles	3
Horsepower Rating	25 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Disconnect Type	Associated circuit breaker
Circuit breaker CT rating	50 A
Circuit breaker type	HLL
Thermal overload type	Motor Logic solid state class 10/20
Protection type	Overload Phase loss Phase unbalance
Device mounting	Surface
Electrical connection	Screw terminal
NEMA size	2
Height	38.50 in (978 mm)
Width	20.43 in (519 mm)
Depth	9.41 in (239 mm)

Environment

NEMA Rating	NEMA 3R
Enclosure type	Weatherproof enclosure indoor/outdoor
Product certifications	UL Listed NEMA

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	21395 - 8940 XC,XD
Discount Schedule	CP1
GTIN	00785901121268
Nbr. of units in pkg.	1
Package weight(Lbs)	89 lb(US) (40.37 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	1.08 ft (0.330 m)
Package 1 width	1.79 ft (0.546 m)
Package 1 Length	3.42 ft (1.041 m)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------