



POWERING YOUR *life.*

Model 100231

UPC 850878006198

Warranty 3 Years

6900

STARTING WATTS
Propane: 6250

5500

RUNNING WATTS
Propane: 5000

RUN TIME
9 hrs.

RUN TIME
6.5 hrs.

NOISE LEVEL
74 dBA

INTELLI GAUGE
3-MODE display

VOLT GUARD
Protects against **POWER SURGES**

COLD START
Easy starts in **COLD WEATHER**

Receptacles



30 AMP
120/240V, L14-30R



20 AMP GFCI
120V, 5-20R



20 AMP GFCI
120V, 5-20R



Specifications

START TYPE	Recoil
VOLTAGE (V) AC	120/240
VOLTMETER	Intelligauge
ENGINE SIZE (cc)	389
FUEL TYPE	Gasoline or Propane
GASOLINE CAPACITY (gal.)	6.0
OIL TYPE	10W-30
OIL CAPACITY (fl. oz./mL)	37.2/1100
LOW OIL SHUT-OFF	Yes
EMISSIONS	EPA III/CARB

Versatile and convenient power is yours with the Champion 5500-watt portable generator. Dual Fuel Technology allows the 389cc engine to run on your choice of gasoline or propane. This unit includes a propane hose, and provides up to 9 hours of run time on gasoline or 6.5 hours on propane.

Inside the box

- GENERATOR
- WHEEL KIT
- PROPANE HOSE 6.5 FT.
- OPERATOR'S MANUAL
- OIL FUNNEL

What You Need

- GASOLINE OR PROPANE
- WRENCH/SOCKET SET
- PLIERS
- ENGINE OIL (10W-30)

*Specifications, descriptions and illustrations are subject to change without notice.

PACKAGE (gross)
Weight: 174.4 lb.
Size: 30.7 x 22.6 x 23.2 in.

PRODUCT (net)
Weight: 162.5 lb.
Size: 27 x 27.7 x 24.4 in.

CHAMPION POWER EQUIPMENT, INC.
12039 Smith Ave., Santa Fe Springs, CA 90670, USA
www.championpowerequipment.com