

Product data sheet

Characteristics

T02FN13G7

NEMA Contactor, TeSys N, nonreversing, Size 4, 135A, 100HP at 460VAC, 3 pole, 3 phase, 120VAC 50/60Hz coil, open



Main

Product Type	Contacteur
Range	TeSys N
Contacteur Type	Non-reversing
NEMA Size	4
Motor Horsepower Rating HP	40 Hp 200 V AC 50 Hp 230 V AC 100 Hp 460 V AC 100 hp 575 V AC

Complementary

Rated Current	135 A
[Ue] Rated Operational Voltage	600 V AC
Network Phases	3 phase
Number of Poles	3P
Control Circuit	Common control circuit
Coil Voltage	120 V AC
Auxiliary Contact Composition	1 NO
Electrical Connection	Lugs ordered separately
Height	6.69 in (169.93 mm)
Width	6.44 in (163.58 mm)
Depth	6.68 in (169.67 mm)
Product Weight	9.40 lb(US) (4.26 kg)

Environmental

Product Certifications	UL Listed CSA
NEMA Degree of Protection	Not rated (open device)

Ordering and shipping details

Category	21197 - TESYS N CONTACTORS SIZES 3 - 7
Discount Schedule	CP1
GTIN	00785901429333
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	US

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.