

Product data sheet

Characteristics

HOM3060M200PQCVP

Load center, Homeline, 1 phase, 30 spaces, 60 circuits, 200A convertible main breaker, PoN, NEMA1, Qwik-grip, value pack



Main

Product Type	Load Center value pack
Marketing Trade Name	Homeline
Load Center Type	Main breaker
Rated Current	200 A
Number of Spaces	30
Maximum Number of Single Pole Circuits	60
Enclosure Rating	NEMA 1 for indoor
Cover Type	Combination flush/surface cover
Electrical Connection	Lugs
Provided Equipment	Circuit breaker 1) 2P 200 A 120/240 V AC main supply ready assembled Circuit breaker 3) 1P 20 A 120/240 V AC Circuit breaker 2) 2P 30 A 120/240 V AC Load center 1) Qwik grip assembly kit 1)

Complementary

Max Short Circuit Current Rating	10 kA
Maximum Number of Tandem Breakers	30
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 4...250 kcmil aluminium/copper
Ground Bar	Grounding bar (ordered separately)
Wiring Configuration	3-wire
Enclosure Material	Welded galvanized steel
Surface Finish	Baked enamel grey
Box Number	10Q
Height	33.78 in (858 mm)
Depth	3.74 in (95 mm)
Width	14.25 in (362 mm)

Environment

Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
---------------------------------------	---------------------------------

Ordering and shipping details

Category	00185 - MISC. HOM LOAD CENTERS
Discount Schedule	DE3C
GTIN	00785901641407
Nbr. of units in pkg.	1
Package weight(Lbs)	34.7 lb(US) (15.74 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	0.80 in (2.032 cm)
Package 1 width	1.80 in (4.572 cm)
Package 1 Length	2.50 in (6.350 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration