



POWERING YOUR *life.*

Model 201122

UPC 817198025742

Warranty 3 Years

2500
STARTING WATTS
Propane: 2500

1850
RUNNING WATTS
Propane: 1665

RUN TIME 11.5 hrs. **RUN TIME** 34 hrs. **NOISE LEVEL** 53 dBA

EZ START DIAL
Confusion free **ENGINE START-UP**

ULTRA QUIET
LOW NOISE - high performance

ULTRALIGHT
Compact design weighs **LESS THAN 40 LB.**

PARALLEL READY
Link 2 units for **DOUBLE POWER**

Receptacles



20 AMP
120V, 5-20R



Parallel



USB
5V 2.1A (x2)

Specifications

START TYPE	Recoil
VOLTAGE (V) AC	120
DC VOLTS	5.0
ENGINE SIZE (cc)	79
FUEL TYPE	Gasoline or Propane
GASOLINE CAPACITY (gal.)	1.1
OIL TYPE	10W-30
OIL CAPACITY (fl. oz./mL)	16.9/500
LOW OIL SHUT-OFF	Yes
EMISSIONS	EPA III/CARB



CARBON MONOXIDE AUTO-SHUTOFF SYSTEM



OIL INCLUDED



Our 2500-watt inverter is one of the lightest in the industry, meets ANSI/PGMA G300-2018 requirements, and features CO Shield, the carbon monoxide auto shutoff system. Featuring Dual Fuel, allowing the 79cc engine to run on gasoline or propane, it provides up to 11.5 hours on gasoline or up to 34 hours with a 20-lb propane.

Inside the box

GENERATOR
PROPANE HOSE 2.3 FT.
OPERATOR'S MANUAL

What You Need

GASOLINE OR PROPANE

*Specifications, descriptions and illustrations are subject to change without notice.

PACKAGE (gross)
Weight: 48.5 lb.
Size: 19.1 x 13.4 x 20.1 in.

PRODUCT (net)
Weight: 39 lb.
Size: 17.3 x 11.5 x 17.7 in.