


Product data sheet

Characteristics

QO132M125P

Load center, QO, 1 phase, 32 spaces, 38 circuits, 125A convertible main breaker, PoN, NEMA1,



Main

Marketing Trade Name	QO
Product Type	Load Center

Complementary

Tightening Torque	Cover: 20 lb.in
Load Center Type	Main breaker
Rated Current	125 A
Number of Spaces	32
Max Short Circuit Current Rating	22 kA
Maximum Number of Single Pole Circuits	38
Maximum Number of Tandem Breakers	6
Number of Phases	1 phase
Ground Bar	Grounding bar (ordered separately)
Box Number	8
Height	26.04 in (661.42 mm)
Width	14.25 in (361.95 mm)
Depth	3.75 in (95.25 mm)

Environment

Enclosure Rating	NEMA 1 for indoor
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)

Ordering and shipping details

Category	10001 - QO PON 1PH LC,12-60 CKT, MB N1
Discount Schedule	DE3A
GTIN	00785901611318
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration