

HC3291WP

HCM 32 INCH WIDE by 91 INCH HIGH TYPE3R/12 I-LINE PANELBOARD ENCLOSURE



Main

Range of product	I-Line
Product or component type	Enclosure
Device application	Panelboard
Device short name	HCM

Complementary

Line Rated Current	225 A 400 A 600 A 800 A
Enclosure nominal width	32.01 in (813 mm)
Enclosure nominal height	90.98 in (2311 mm)
Enclosure nominal depth	9.49 in (241 mm) 8.27 in (210 mm)
Net Weight	284.00 lb(US) (128.82 kg)

Environment

NEMA degree of protection	NEMA 3R/12
Standards	UL CSA

Ordering and shipping details

Category	00110 - RTA PANELBOARD BOXES - SPECIAL, 3R, ETC.
Discount Schedule	PE1A
GTIN	00785901803362
Nbr. of units in pkg.	1
Package weight(Lbs)	338 lb(US) (153.31 kg)
Returnability	No
Country of origin	US

Packing Units

Package 1 Height	1.02 ft (0.312 m)
Package 1 width	2.74 ft (0.836 m)
Package 1 Length	7.68 ft (2.342 m)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------