

Product data sheet

Characteristics

QOMB1100

Load center accessory, QO, mounting base, OEM, 1 pole, NEMA1, quantity 100



Main

Marketing Trade Name	QO
Product Type	Mounting base

Complementary

Load Center Type	Main lugs
Rated Current	100 A
Number of Spaces	1
Max Short Circuit Current Rating	10 kA
Maximum Number of Single Pole Circuits	1
Maximum Number of Tandem Breakers	0
Number of Phases	1 phase
Wire Size	AWG 14...AWG 4 copper AWG 12...AWG 2 aluminium
Wiring Configuration	2-wire
Height	1.718 in (43.64 mm)
Width	4.718 in (119.84 mm)
Depth	0.687 in (17.45 mm)

Environment

Enclosure Rating	NEMA 1 for indoor
Product Certifications	UL Listed

Ordering and shipping details

Category	00909 - MOUNTING BASES, S/N
Discount Schedule	DE3A
GTIN	00785901082194
Nbr. of units in pkg.	1
Package weight(Lbs)	7.52 lb(US) (3.41 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	6.40 in (16.256 cm)
Package 1 width	10.20 in (25.908 cm)
Package 1 Length	11.40 in (28.956 cm)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------