

# SF 682



## SHURFLEX® NON-PRINTED METALIZED CLOTH DUCT TAPE

### TYPICAL APPLICATIONS

- For use in the HVAC industry for airtight and moisture-free seaming, connecting, splicing, patching and sealing of sheet metal and flex duct, rigid duct boards, air vents, insulation, fibrous filter banks and pollution collection systems

### PRODUCT FEATURES

- Designed to match sheet metal, flex duct and duct board
- Flexible and conformable
- Easy to unwind and tear
- Will not twist or curl during application
- Hand-tearable
- No release liner to discard

### CONSTRUCTION

Overall Grade/Function: HVAC  
Backing: Waterproof, metalized polyethylene film with a cloth carrier  
Adhesive: Natural rubber

### STANDARD WIDTH(S)

48 mm    72 mm

### STANDARD LENGTH(S)

55 m  
Contact your Shurtape sales representative for other available sizes

### STANDARD CORE SIZE

3 in

### APPLICABLE STANDARDS

Tested in accordance with UL 723

### COLOR(S)



PHYSICAL PROPERTIES	STANDARD	METRIC
Tensile Strength	26 lbs/in width	45.5 N/10 mm
Adhesion to Stainless Steel	55 oz/in width	6.02 N/10 mm
Thickness	10 mils	0.25 mm
Elongation	23%	23%
Service Temperature Range	50 F to 200 F	10 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

### STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

