

PG20

30 DAY UV-RESISTANT PREMIUM PAPER MASKING TAPE

INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

DESCRIPTION

An aluminized, silver, saturated crepe paper backing protects the specially formulated, high temperature resistant, pressure-sensitive natural rubber adhesive from the effects of ultraviolet light. Can be used in outdoor applications for periods of up to one month depending on the weather conditions and the surface to which the tape is applied.

PRODUCT APPLICATION

Windshield repair/replacement for automotive, truck, bus and marine.

NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

Backing	Aluminized Crepe Paper
Adhesive	Natural Rubber/Resin
Adhesion to Steel (oz/in of width)	30 (8 N/25mm)
Tensile Strength (lbs/in of width)	23 (101 N/25mm)
Elongation (% at break)	8
Total Thickness (mils)	6.8 (0.17mm)
Quick Stick (oz/in of width)	
To Kraft	7 (1.9 N/25mm)
To Steel	16 (4.4 N/25mm)
Operating Temperature Range	50°F ~ 325°F (10°C ~ 163°C)
Color	Silver



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA

Customer Service: 800.IPG.8273 | 800.474.8273

Tape Technical Service: 877.447.4832

www.itape.com | info@itape.com



While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 09/18

