

Product data sheet

Characteristics

JJA34250WU31X

Circuit breaker, PowerPacT J, I-Line,
Micrologic 3.2, 250A, 3 pole, 65 kA, 480 VAC,
phase ABC



Complementary

Number of Poles	3P
Breaking capacity code	J
Magnetic hold current	1250 A
Magnetic tripping current	2500 A
Electrical connection	I-Line connection line Lugs load
Tightening torque	230.12 lbf.in (26 N.m) 0.15...0.29 in ² (95...185 mm ²) (AWG 3/0...350 kcmil)
Phase connection	ABC
Height	11.48 in (291.59 mm)
Width	4.48 in (113.79 mm)
Depth	5.87 in (149.10 mm)
Continuous current rating	80 %

Ordering and shipping details

Category	01104-H/J ELEC TRIP I-LINE BREAKER / SW
Discount Schedule	DE2
Package weight(Lbs)	5.00 lb(US) (2.268 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.