



Main

Range	Lineryg
Product name	HK
Product or component type	Busbar
Device application	Distribution
Tap-offs (18 mm)	24
Bar length	22.05 in (560 mm)
Enclosure/cubicle width	800 mm
Network type	AC
[Ie] rated operational current	160 A 95 °F (35 °C)
[Ue] rated operational voltage	400 V off-load plugging-in and unplugging, with supply switched on)IEC 60439-1 480 V off-load plugging-in and unplugging, with supply switched on)CSA 480 V off-load plugging-in and unplugging, with supply switched on)UL 600 V plugging-in and unplugging, with supply switched off)CSA 600 V plugging-in and unplugging, with supply switched off)UL 690 V plugging-in and unplugging, with supply switched off)IEC 60439-1
Number of conductors	4

Complementary

Bar width	1.77 in (45 mm)
Width	3.19 in (81 mm)
Depth	3.23 in (82 mm)
Network frequency	50/60 Hz
[Ui] rated insulation voltage	600 V CSA 600 V UL 690 V IEC 60439-1
Peak current	25 kA
I ² t on activation	10000000 A ² .s
Protection type	AM fuses In = 160 A, I _{sc} = 100 kA, I _e = 160 A GF fuses In = 160 A, I _{sc} = 100 kA, I _e = 160 A NS160H circuit breaker In = 160 A, I _{sc} = 36 kA, I _e = 160 A NS160H circuit breaker In = 160 A, I _{sc} = 70 kA, I _e = 160 A
Connections - terminals	Connector 0.00...0.11 in ² (2.5...70 mm ²) flexible with cable end Connector 0.00...0.11 in ² (2.5...70 mm ²) rigid
Tightening torque	88.51 lbf.in (10 N.m)
Mounting position	Vertical using side stop AK5BT01 on mounting plates AK5PA Horizontal
Flame retardance	V0 conforming to UL 94
Net Weight	2.43 lb(US) (1.1 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	IEC 60439
Product certifications	DNV CSA UL LROS (Lloyds register of shipping)
IP degree of protection	IPxx B conforming to IEC 60529
Fire resistance	1562 °F (850 °C) IEC 60695

Ordering and shipping details

Category	22623 - PANEL BUS (AK5)
Discount Schedule	I11
GTIN	00785901576785
Nbr. of units in pkg.	1
Package weight(Lbs)	2.8 lb(US) (1.27 kg)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.21 in (10.7 cm)
Package 1 width	4.33 in (11 cm)
Package 1 Length	29.17 in (74.1 cm)
Unit Type of Package 2	P06
Number of Units in Package 2	20
Package 2 Weight	96.56 lb(US) (43.8 kg)
Package 2 Height	31.50 in (80 cm)
Package 2 width	31.50 in (80 cm)
Package 2 Length	23.62 in (60 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------