

Product data sheet

Characteristics

QO2L70S

Load center, QO, 1 phase, 2 spaces, 2 circuits, 70A fixed main lugs, NEMA1, surface cover, UL



Main

Marketing Trade Name	QO
Product Type	Load Center
Cover Type	Surface cover

Complementary

Load Center Type	Main lugs
Rated Current	70 A
Number of Spaces	2
Max Short Circuit Current Rating	10 kA
Maximum Number of Single Pole Circuits	2
Maximum Number of Tandem Breakers	0
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Ground Bar	Grounding bar (ordered separately)
Electrical Connection	Lugs
Wiring Configuration	3-wire
Busbar Material	Tin plated aluminium busbar
Enclosure Material	Welded sheet steel
Height	9.17 in (233 mm)
Width	4.69 in (119 mm)
Depth	3.11 in (79 mm)

Environment

Enclosure Rating	NEMA 1 for indoor
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	CULus

Ordering and shipping details

Category	00156 - CANADIAN LOAD CTRS
Discount Schedule	DE3A
GTIN	00785901707738
Nbr. of units in pkg.	1
Package weight(Lbs)	3.86 lb(US) (1.75 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	4.20 in (10.668 cm)
Package 1 width	5.40 in (13.716 cm)
Package 1 Length	10.20 in (25.908 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------