



Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1D6
Control circuit type	AC at 50/60 Hz
[Uc] control circuit voltage	220 V AC 50/60 Hz
Average resistance	102 Ohm 68 °F (20 °C)
Inductance of closed circuit	6.7 H
Product compatibility	LC1D80 LC1D95
Mechanical durability	4 Mcycles
Maximum operating rate	3600 cyc/h 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out 0.3...0.6 Uc 50/60 Hz 131 °F (55 °C) Operational 0.8...1.1 Uc 50 Hz 131 °F (55 °C) Operational 0.85...1.1 Uc 60 Hz 131 °F (55 °C)
Inrush power in VA	245 VA 60 Hz 0.75 68 °F (20 °C) 245 VA 50 Hz 0.75 68 °F (20 °C)
Hold-in power consumption in VA	26 VA 60 Hz 0.3 68 °F (20 °C) 26 VA 50 Hz 0.3 68 °F (20 °C)
Heat dissipation	6...10 W 50/60 Hz

Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Net Weight	0.62 lb(US) (0.28 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901260318
Nbr. of units in pkg.	1
Package weight(Lbs)	0.69 lb(US) (0.31 kg)
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.20 in (5.6 cm)
Package 1 width	4.92 in (12.5 cm)
Package 1 Length	3.54 in (9 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	16
Package 2 Weight	11.81 lb(US) (5.358 kg)
Package 2 Height	5.91 in (15 cm)

Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Contractual warranty

Warranty	18 months
----------	-----------
