PG505

UTILITY PAPER MASKING TAPE

INTERTAPE POLYMER GROUP®

TECHNICAL DATA SHEET

DESCRIPTION

A paint contractor industry staple. Crepe paper masking tape coated with a pressure-sensitive natural rubber adhesive. Offers an excellent balance of quick stick, panel adhesion and holding properties. Not recommended for outdoor exposure.

PRODUCT APPLICATION

For general purpose masking.

GOVERNMENT COMPLIANCE

ASTM D6123, Type I C.I.D. A-A-883B Type I

STORAGE RECOMMENDATION

Store new stock behind current stock. Store in a clean, dry place. Temperature of 70°F (21°C) +/- 6°F, and 40% to 50% relative humidity are recommended.

SHELF LIFE

When stored under recommended conditions, converted rolls have an expected shelf life of up to one (1) year from the date of shipment. Jumbo rolls have the same expected shelf life, but it is recommended that they are converted within six (6) months of date of shipment.

intertape polymer group®

100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA Customer Service: 800.IPG.8273 | 800.474.8273

Tape Technical Service: 877.447.4832 www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 04/16

NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

| Backing | Crepe Paper |
|--|-----------------------------------|
| Adhesive | Natural Rubber/Resin |
| Adhesion to Steel (oz/in of width) PSTC-101 | 33 (9.0 N/25mm) |
| Tensile Strength (lbs/in of width) PSTC-131 | 20 (87.5 N/25mm) |
| Elongation (% at break) PSTC-131 | 10 |
| Total Thickness (mils) PSTC-133 | 5.8 (0.147mm) |
| Quick Stick (oz/in of width) PSTC-5 | |
| To Kraft To Steel | 5 (1.4 N/25mm) 11 (2.7 N/25mm) |
| Operating Temperature Range | +50°F ~ +200°F (+10°C ~ +93°C) |
| Colors | Beige, Orange |

