

1. Identification

Product identifier	Clorox® Disinfecting Mist Multi-Surface - Lemon Orange Blossom		
Other means of identification	EPA 5813-73		
	Document Number: USA002061		
Recommended use	Disinfectant		
Recommended restrictions	None known.		
Manufacturer/Importer/Supplier/Distributor information			
Manufacturer			
Company name	The Clorox Company		
Address	1221 Broadway Oakland, CA 94612 United States		
Telephone	1-510-271-7000		
E-mail	Not available.		
Emergency phone number	Medical Emergency:	1-800-446-1014	
	Transportation Emergency:	1-800-424-9300 (Chemtrec)	

2. Hazards Identification

Physical hazards	Not classified.
Health hazards	Not classified.
Environmental hazards	Not classified.
OSHA defined hazards	Not classified.
Label elements	
Hazard symbol	None.
Signal word	None.
Hazard statement	The mixture does not meet the criteria for classification.
Precautionary statement	
Prevention	Observe good industrial hygiene practices.
Response	Wash hands after handling.
Storage	Store away from incompatible materials.
Disposal	Dispose of container in accordance with local, regional, national and international regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	This SDS is designed for workplace employees, emergency personnel and for other conditions and situations where there is greater potential for large-scale or prolonged exposure. This SDS is not applicable for consumer use of our products. For consumer use, all precautionary and first aid language is provided on the product label in accordance with the applicable government regulations.

3. Composition/Information on Ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Alkyl (C12 40; C14 50%; C16, 10%) dimethyl benzyl ammonium chloride		68424-85-1	0.3

All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

Composition comments US GHS: The exact percentage (concentration) of composition has been withheld as a trade secret in accordance with paragraph (i) of §1910.1200.

4. First Aid Measures

Inhalation	If breathed in, move person into fresh air.
Skin contact	IF ON SKIN OR CLOTHING: Take off contaminated clothing. Rinse skin immediately with plenty of water for 15-20 minutes. Call a poison control centre or doctor for treatment advice.

Eye contact	IF IN EYES: Hold eye open and rinse slowly and gently with water for 15-20 minutes. Remove contact lenses if present, after the first 5 minutes, then, continue rinsing eye. Call a poison control center or doctor for treatment advice.
Ingestion	If swallowed, call a Poison Control Center or doctor immediately. DO NOT induce vomiting.
Most important symptoms/effects, acute and delayed	Direct contact with eyes may cause temporary irritation.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Symptoms may be delayed. For further information, call (800) 227-1860
General information	If you feel unwell, seek medical advice (show the label where possible). Show this safety data sheet to the doctor in attendance. Avoid contact with eyes and skin. KEEP OUT OF REACH OF CHILDREN AND PETS. Have the product container or label with you when calling a poison control center or doctor, or going for treatment.

5. Fire Fighting Measures

Suitable extinguishing media	Treat for surrounding material.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	Move containers from fire area if you can do so without risk.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	No unusual fire or explosion hazards noted.

6. Accidental Release Measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Prevent entry into waterways, sewer, basements or confined areas. Before attempting clean up, refer to hazard data given above. Small spills may be absorbed with non-reactive absorbent and placed in suitable, covered, labelled containers. Prevent large spills from entering sewers or waterways. Contact emergency services and supplier for advice. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid release to the environment. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground. Do not discharge into lakes, streams, ponds or public waters.

7. Handling and Storage

Precautions for safe handling	Avoid contact with eyes, skin or clothing. Avoid contact with foods. Provide adequate ventilation. Wear appropriate personal protective equipment. Wash thoroughly after handling. Use good industrial hygiene practices in handling this material. When using do not eat or drink.
Conditions for safe storage, including any incompatibilities	Store in a cool, dry, well-ventilated place. Keep in original container. Do not reuse containers. Store away from incompatible materials (see Section 10 of the SDS). KEEP OUT OF REACH OF CHILDREN.

8. Exposure Controls/Personal Protection

Biological limit values	No biological exposure limits noted for the ingredient(s).
Appropriate engineering controls	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.
Individual protection measures, such as personal protective equipment	
Eye/face protection	Not normally required under normal use conditions. If splashes are likely to occur, wear: Wear safety glasses with side shields.
Skin protection	
Hand protection	Not normally required when used as directed. For prolonged use, wear rubber gloves.
Other	Wear appropriate chemical resistant clothing. As required by employer code.

Respiratory protection	Where exposure guideline levels may be exceeded, use an approved NIOSH respirator. Respirator should be selected by and used under the direction of a trained health and safety professional following requirements found in OSHA's respirator standard (29 CFR 1910.134), CAN/CSA-Z94.4 and ANSI's standard for respiratory protection (Z88.2).
Thermal hazards	Not applicable.
General hygiene considerations	Wash hands before breaks and immediately after handling the product. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. When using do not eat or drink.

9. Physical and Chemical Properties

Appearance	Clear
Physical state	Liquid.
Form	Liquid
Color	Clear
Odor	Not available.
Odor threshold	Not available.
pH	9 - 11.5
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Pour point	Not available.
Specific gravity	Not available.
Partition coefficient (n-octanol/water)	Not available.
Flash point	> 200.0 °F (> 93.3 °C)
Evaporation rate	Not available.
Flammability (solid, gas)	Not applicable.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	Not available.
Vapor density	Not available.
Relative density	Not available.
Solubility(ies)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.

10. Stability and Reactivity

Reactivity	This product may react with strong oxidizing agents.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Chemical stability	Material is stable under normal conditions.
Conditions to avoid	Do not mix with other chemicals.
Incompatible materials	Oxidizers. Acids.
Hazardous decomposition products	May include and are not limited to: Oxides of carbon. Oxides of nitrogen. Ammonia. Chlorine gas.

11. Toxicological Information

Information on likely routes of exposure

Inhalation	No adverse effects due to inhalation are expected. Excessive intentional inhalation may cause respiratory tract irritation.
Skin contact	Not expected to be a primary skin irritant.

Eye contact	Direct contact with eyes may cause temporary irritation.	
Ingestion	May cause stomach distress, nausea or vomiting.	
Symptoms related to the physical, chemical and toxicological characteristics	There are no hazards associated with this product in normal use. Direct contact with eyes may cause temporary irritation.	
Information on toxicological effects		
Acute toxicity	See below.	
Components	Species	
Alkyl (C12 40; C14 50%; C16, 10%) dimethyl benzyl ammonium chloride (CAS 68424-85-1)		
Acute		
<i>Dermal</i>		
LD50	Rabbit	3412 mg/kg, ECHA
<i>Inhalation</i>		
LC50	Rat	0.3 mg/l/4h, ECHA
<i>Oral</i>		
LD50	Rat	795 mg/kg, ECHA
Skin corrosion/irritation	Not expected to be a primary skin irritant.	
Exposure minutes	Not available.	
Erythema value	Not available.	
Oedema value	Not available.	
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.	
Corneal opacity value	Not available.	
Iris lesion value	Not available.	
Conjunctival reddening value	Not available.	
Conjunctival oedema value	Not available.	
Recover days	Not available.	
Respiratory or skin sensitization		
Respiratory sensitization	Not available.	
Skin sensitization	Not available.	
Germ cell mutagenicity	Not available.	
Carcinogenicity		
IARC Monographs. Overall Evaluation of Carcinogenicity		
Not listed.		
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)		
Not regulated.		
US. National Toxicology Program (NTP) Report on Carcinogens		
Not listed.		
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.	
Specific target organ toxicity - single exposure	Not available.	
Specific target organ toxicity - repeated exposure	Not available.	
Aspiration hazard	Not an aspiration hazard.	
Chronic effects	Not available.	
Further information	Not available.	

12. Ecological Information

Ecotoxicity	See below		
Ecotoxicological data			
Components	Species		
Alkyl (C12 40; C14 50%; C16, 10%) dimethyl benzyl ammonium chloride (CAS 68424-85-1)			
Aquatic			
Fish	LC50	Striped bass (<i>Morone saxatilis</i>)	10.4 - 19.1 mg/L, 96 hours
Persistence and degradability	Not available.		

Bioaccumulative potential	Not available.
Mobility in soil	Not available.
Mobility in general	Not available.
Other adverse effects	Not available.

13. Disposal Considerations

Disposal instructions	Review federal, provincial, and local government requirements prior to disposal. If recycling is not available, discard in trash.
Waste from residues / unused products	Not available.
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport Information

General	<p>Canada: TDG Proof of Classification: Classification Method: Classified as per Part 2, Sections 2.1 – 2.8 of the Transportation of Dangerous Goods Regulations. If applicable, the technical name and the classification of the product will appear below.</p> <p>Canada: TDG: Not regulated as dangerous goods.</p> <p>US: DOT: Not regulated as dangerous goods.</p> <p>IMDG: Not regulated as dangerous goods.</p> <p>IATA: Not regulated as dangerous goods.</p>
----------------	--

15. Regulatory Information

US federal regulations	<p>This product is NOT known to be a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.</p> <p>This chemical is a disinfectant product registered by the United States Environmental Protection Agency and is subject to certain labeling requirements under federal pesticide law. These requirements differ from the classification criteria and hazard information required for safety data sheets (SDS), and for workplace labels of non-disinfectant chemicals. The hazard information required on the disinfectant label is reproduced below. The disinfectant label also includes other important information, including directions for use.</p> <p>It is a violation of Federal law to use this product in a manner inconsistent with its labeling.</p> <p>EPA 5813-73</p> <p>PRECAUTIONARY STATEMENTS: HAZARDS TO HUMANS AND DOMESTIC ANIMALS</p> <p>CAUTION: Causes moderate eye irritation. Avoid contact with eyes, skin or clothing. Wash thoroughly with soap and water after handling. Avoid contact with foods.</p> <p>TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D) Not regulated.</p> <p>CERCLA Hazardous Substance List (40 CFR 302.4) Not listed.</p> <p>SARA 304 Emergency release notification Not regulated.</p> <p>OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052) Not regulated.</p> <p>Superfund Amendments and Reauthorization Act of 1986 (SARA)</p> <table> <tr> <td>SARA 302 Extremely hazardous substance</td> <td>No</td> </tr> <tr> <td>SARA 311/312 Hazardous chemical</td> <td>No</td> </tr> <tr> <td>SARA 313 (TRI reporting)</td> <td>Not regulated.</td> </tr> </table> <p>Other federal regulations</p> <p>Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List Not regulated.</p>	SARA 302 Extremely hazardous substance	No	SARA 311/312 Hazardous chemical	No	SARA 313 (TRI reporting)	Not regulated.
SARA 302 Extremely hazardous substance	No						
SARA 311/312 Hazardous chemical	No						
SARA 313 (TRI reporting)	Not regulated.						

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

US state regulations See below

US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)

Not listed.

California Proposition 65

This product is not subject to warning labeling under the California Proposition 65 regulation.


Country(s) or region	Inventory name	On inventory (yes/no)*
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	No

*A "Yes" indicates this product complies with the inventory requirements administered by the governing country(s)

16. Other Information

LEGEND	
Severe	4
Serious	3
Moderate	2
Slight	1
Minimal	0

HEALTH	/ 1
FLAMMABILITY	0
PHYSICAL HAZARD	0
PERSONAL PROTECTION	X



Disclaimer

The information in the safety data sheet was written by Dell Tech Laboratories Ltd. (www.delltech.com) based on the best knowledge and experience currently available. Information contained herein was obtained from sources considered technically accurate and reliable. While every effort has been made to ensure full disclosure of product hazards, in some cases data is not available and is so stated. Since conditions of actual product use are beyond control of the supplier, it is assumed that users of this material have been fully trained according to the requirements of all applicable legislation and regulatory instruments. No warranty, expressed or implied, is made and supplier will not be liable for any losses, injuries or consequential damages which may result from the use of or reliance on any information contained in this document.

Issue date 06-January-2022

Version # 01

Further information Not available.

Other information For an updated SDS, please contact the supplier/manufacturer listed on the first page of the document.

Reference Item: 513274.001

Prepared by: The Clorox Company, 4900 Johnson Drive, Pleasanton, CA 94588, 925-368-6000