



Main

Range	TeSys
Device short name	LUF
Product or component type	Function module
Product compatibility	LUCB LUCC LUCD

Complementary

Mounting mode	Plug-in
Mounting location	Front side
Main function available	Thermal overload signalling and automatic or remote reset
Auxiliary contact composition	1 NC
Communication of faults	LED front panel
[Us] rated supply voltage	24...240 V DC
[Ith] conventional free air thermal current	2 A 158 °F (70 °C)
Short-circuit protection	2 A fuse gG IEC 60947-5-1
Connection pitch	0.20 in (5.08 mm)
Tightening torque	4.43...5.31 lbf.in (0.5...0.6 N.m) 0.14 in (3.5 mm) flat
Net Weight	0.12 lb(US) (0.055 kg)

Ordering and shipping details

Category	22399 - TESYS U, ACCESSORIES
Discount Schedule	I11
GTIN	00785901806899
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.30 in (3.3 cm)
Package 1 width	1.85 in (4.7 cm)
Package 1 Length	4.13 in (10.5 cm)
Unit Type of Package 2	S01
Number of Units in Package 2	20
Package 2 Weight	3.85 lb(US) (1.748 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------