




6540.170 Shown



GENERAL DESCRIPTION:

Durable cast brass construction. Cast brass valve bodies with 8" rigid copper connection with compression fittings. 1/2" male threaded inlet shanks with brass coupling nuts. 1/4 turn ceramic disc valve cartridges. Convertible rigid/swivel spout. Choice of Vandal-Resistant Lever or Wrist Blade handles with blue & red color indexes. All brass drain bodies with 1 1/4" (32mm) tailpieces (on applicable models). 1.5 gpm/5.7L/min. maximum flow rate. Vandal-Resistant and Laminar Flow aerators are available.

PRODUCT FEATURES:

- Pressure Compensating Aerator:** Provides a constant water flow of 1.5 gpm throughout the pressure range.
- Solid Brass Construction:** Durable - Excellent in high use applications. Ideal for prolonged contact with water.
- Ceramic Disc Valve Cartridges:** Assures a lifetime of drip-free performance.
- Field-Convertible Rigid/Swivel Spout:** Easily converted in the field.
- Lead Free:** Faucet contains ≤ 0.25% total lead content by weighted average.

MODEL NUMBER:

- 6540.170 Widespread Lavatory**
1.5 gpm Pressure Compensating Aerator. Convertible rigid/swivel gooseneck spout. Vandal-Resistant Wrist Blade Handles. Less drain and pop-up hole.
- 6542.170 Widespread Lavatory**
1.5 gpm Pressure Compensating Aerator. Convertible rigid/swivel gooseneck spout. Vandal-Resistant Wrist Blade Handles. Grid strainer drain.
- 6540.140 Widespread Lavatory**
1.5 gpm Pressure Compensating Aerator. Convertible rigid/swivel gooseneck spout. Vandal-Resistant Lever Handles. Less drain and pop-up hole.
- 6542.140 Widespread Lavatory**
1.5 gpm Pressure Compensating Aerator. Convertible rigid/swivel gooseneck spout. Vandal-Resistant Lever Handles. Grid strainer drain.


SUGGESTED SPECIFICATION:

Two handle widespread lavatory faucet shall feature cast brass valve bodies with 8" rigid copper connection. Shall feature water-conserving 1.5 gpm/5.7L/min. pressure compensating aerator. Vandal-Resistant handles. Shall also feature 1/4 turn washerless ceramic disc valve cartridges. Shall also feature convertible rigid/swivel spout. Fitting shall be American Standard Model # 654_._.002.

CODES AND STANDARDS

These products meet or exceed the following codes and standards:

- ASME A112.18.1**
- CSA B 125**
- NSF 61/Section 9 and Annex G**



| Product Number | Description | Finish |
|----------------|--|-----------------|
| | | Polished Chrome |
| | | 002 |
| 6540.170 | Widespread Lavatory with convertible rigid/swivel gooseneck spout. 1.5 gpm/5.7L/min pressure compensating aerator. Vandal-Resistant Wrist Blade Handles. Less drain and pop-up hole. | |
| 6542.170 | Widespread Lavatory with convertible rigid/swivel gooseneck spout. 1.5 gpm/5.7L/min pressure compensating aerator. Vandal-Resistant Wrist Blade Handles. Grid strainer drain. | |
| 6540.140 | Widespread Lavatory with convertible rigid/swivel gooseneck spout. 1.5 gpm/5.7L/min pressure compensating aerator. Vandal-Resistant Lever Handles. Less drain and pop-up hole. | |
| 6542.140 | Widespread Lavatory with convertible rigid/swivel gooseneck spout. 1.5 gpm/5.7L/min pressure compensating aerator. Vandal-Resistant Lever Handles. Grid strainer drain. | |

 **MEETS THE AMERICANS WITH DISABILITIES ACT GUIDELINES AND ANSI A117.1 REQUIREMENTS FOR ACCESSIBLE AND USABLE BUILDING FACILITIES-CHECK LOCAL CODES**

Other Aerators Available:

| Part Suffix | Description |
|-------------|---|
| LV22 | 2.2 gpm (8.3 Lpm) Vandal-Resistant Non-Aerated Laminar Flow Outlet |
| V22 | 2.2 gpm (8.3 Lpm) Vandal-Resistant Aerator |
| A15LV | Anti-Microbial 1.5 gpm (5.7 Lpm) Vandal-Resistant Non-Aerated Laminar Flow Outlet |
| LV15 | 1.5 gpm (5.7 Lpm) PCA Vandal-Resistant Non-Aerated Laminar Flow Outlet |
| V15 | .5 gpm (5.7 Lpm) PCA Vandal-Resistant Aerator |
| LV10 | 1.0 gpm (3.8 Lpm) PCA Vandal-Resistant Non-Aerated Laminar Flow Outlet |
| V10 | 1.0 gpm (3.8 Lpm) PCA Vandal-Resistant Aerator |
| V05 | 0.5 gpm (1.9 Lpm) PCA Vandal-Resistant Non-Aerated Spray |
| V035** | 0.35 gpm (1.3 Lpm) PCA Vandal-Resistant Non-Aerated Spray |

*PCA - Pressure Compensating

**Meets Cal Green Code