



Main

Product	Energy Efficient Transformer
Enclosure Code	17D
Enclosure Type	NEMA 2
Insulation Temperature	428 °F (220 °C)
Phase	1 phase
Primary Voltage	240 x 480 V
Power Rating	15 kVA
Secondary Voltage	120/240 V
Full Capacity Taps	6 2.5 % 2+ 4-
Temperature Rise	150 °C
Winding Material	Aluminium

Complementary

Height	27 in (685.80 mm)
Width	20 in (508.00 mm)
Depth	16 in (406.40 mm)
Net Weight	214.99 lb(US) (97.52 kg)

Ordering and shipping details

Category	16284 - 1 PH EE/TP1 LVGP XFMR
Discount Schedule	PE2E
GTIN	00785901792468
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	33.30 in (84.582 cm)
Package 1 width	21.40 in (54.356 cm)
Package 1 Length	17.20 in (43.688 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty

18 months

Approximate Dimensions

