

### SECTION 1: Identification

#### 1.1. Identification

Product form : Mixture  
Product name : Gutter Bomb  
Product code : 1192-4737

#### 1.2. Recommended use and restrictions on use

Use of the substance/mixture : Cleaners, liquids (all purpose cleaners, sanitary products, floor cleaners, glass cleaners, carpet cleaners, metal cleaners)

#### 1.3. Supplier

J. Racenstein Co.  
3201 South Harbor Blvd.  
Santa Ana, CA 92704  
T (800) 221-3748

#### 1.4. Emergency telephone number

Emergency number : (800) 535-5053

### SECTION 2: Hazard(s) identification

#### 2.1. Classification of the substance or mixture

##### GHS-US classification

Skin corrosion/irritation Category 2	H315	Causes skin irritation
Serious eye damage/eye irritation Category 1	H318	Causes serious eye damage

Full text of H statements : see section 16

#### 2.2. GHS Label elements, including precautionary statements

##### GHS-US labeling

Hazard pictograms (GHS-US) :



GHS05

Signal word (GHS-US) : Danger  
Hazard statements (GHS-US) : H315 - Causes skin irritation  
H318 - Causes serious eye damage  
Precautionary statements (GHS-US) : P264 - Wash hands and forearms thoroughly after handling  
P280 - Wear protective gloves/eye protection/face protection  
P302+P352 - If on skin: Wash with plenty of soap and water  
P305+P351+P338 - If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P310 - Immediately call a poison center/doctor  
P321 - Specific treatment (see First aid measures on this label)  
P332+P313 - If skin irritation occurs: Get medical advice/attention  
P362+P364 - Take off contaminated clothing and wash it before reuse

#### 2.3. Other hazards which do not result in classification

No additional information available

#### 2.4. Unknown acute toxicity (GHS US)

Not applicable

### SECTION 3: Composition/Information on ingredients

#### 3.1. Substance

Not applicable

# Gutter Bomb

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### 3.2. Mixture

Name	Product identifier	%	GHS-US classification
tetrasodium ethylene diamine tetracetate	(CAS No) 64-02-8	1 - 5	Acute Tox. 4 (Oral), H302 Eye Dam. 1, H318
Disodium metasilicate	(CAS No) 6834-92-0	1 - 5	Skin Corr. 1B, H314 STOT SE 3, H335
Citric acid	(CAS No) 77-92-9	1 - 5	Eye Irrit. 2A, H319

Full text of hazard classes and H-statements : see section 16

## SECTION 4: First-aid measures

### 4.1. Description of first aid measures

- First-aid measures general : Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
- First-aid measures after inhalation : Allow victim to breathe fresh air. Allow the victim to rest.
- First-aid measures after skin contact : Wash with plenty of soap and water. Wash contaminated clothing before reuse. If skin irritation occurs: Get medical advice/attention. Specific treatment (see First aid measures on this label).
- First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a poison center or doctor/physician.
- First-aid measures after ingestion : Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

### 4.2. Most important symptoms and effects (acute and delayed)

- Symptoms/injuries after skin contact : Causes skin irritation.
- Symptoms/injuries after eye contact : Causes serious eye damage.

### 4.3. Immediate medical attention and special treatment, if necessary

No additional information available

## SECTION 5: Fire-fighting measures

### 5.1. Suitable (and unsuitable) extinguishing media

- Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.
- Unsuitable extinguishing media : Do not use a heavy water stream.

### 5.2. Specific hazards arising from the chemical

No additional information available

### 5.3. Special protective equipment and precautions for fire-fighters

- Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire-fighting water from entering environment.
- Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

#### 6.1.1. For non-emergency personnel

- Emergency procedures : Evacuate unnecessary personnel.

#### 6.1.2. For emergency responders

- Protective equipment : Equip cleanup crew with proper protection.
- Emergency procedures : Ventilate area.

### 6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

### 6.3. Methods and material for containment and cleaning up

- Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.

### 6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

# Gutter Bomb

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### SECTION 7: Handling and storage

#### 7.1. Precautions for safe handling

- Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapor.
- Hygiene measures : Wash hands and forearms thoroughly after handling.

#### 7.2. Conditions for safe storage, including any incompatibilities

- Storage conditions : Keep only in the original container in a cool, well ventilated place away from heat, hot surfaces, sparks, open flame and other ignition sources. No smoking. Keep container closed when not in use.
- Incompatible products : Strong bases. Strong acids.
- Incompatible materials : Sources of ignition. Direct sunlight.

### SECTION 8: Exposure controls/personal protection

#### 8.1. Control parameters

Disodium metasilicate (6834-92-0)
Not applicable

Citric acid (77-92-9)
Not applicable

tetrasodium ethylene diamine tetracetate (64-02-8)
Not applicable

#### 8.2. Appropriate engineering controls

No additional information available

#### 8.3. Individual protection measures/Personal protective equipment

##### Personal protective equipment:

Avoid all unnecessary exposure.

##### Hand protection:

Wear protective gloves/eye protection/face protection protective gloves

##### Eye protection:

Chemical goggles or safety glasses

##### Skin and body protection:

Wear suitable protective clothing

##### Respiratory protection:

Wear appropriate mask

##### Other information:

Do not eat, drink or smoke during use.

### SECTION 9: Physical and chemical properties

#### 9.1. Information on basic physical and chemical properties

- Physical state : Liquid
- Color : clear
- Odor : mild
- Odor threshold : No data available
- pH : 10.5 - 11
- Melting point : No data available
- Freezing point : No data available
- Boiling point : 212 - 220 °F

# Gutter Bomb

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Flash point	: > 200 °F
Relative evaporation rate (butyl acetate=1)	: No data available
Flammability (solid, gas)	: Non flammable.
Vapor pressure	: No data available
Relative vapor density at 20 °C	: No data available
Relative density	: 1.06
Solubility	: Soluble in water.
Log Pow	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosion limits	: No data available
Explosive properties	: No data available
Oxidizing properties	: No data available

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No additional information available

### 10.2. Chemical stability

Not established.

### 10.3. Possibility of hazardous reactions

Not established.

### 10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

### 10.5. Incompatible materials

Strong acids. Strong bases.

### 10.6. Hazardous decomposition products

Fume. Carbon monoxide. Carbon dioxide.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Acute toxicity : Not classified

Disodium metasilicate (6834-92-0)	
LD50 dermal rat	> 5000 mg/kg body weight (Rat; Read-across; OECD 402: Acute Dermal Toxicity)
Citric acid (77-92-9)	
LD50 oral rat	3000 mg/kg (Rat; Literature study)
LD50 dermal rat	> 2000 mg/kg body weight (Rat; Experimental value; OECD 402: Acute Dermal Toxicity)
ATE US (oral)	3000.000 mg/kg body weight
tetrasodium ethylene diamine tetracetate (64-02-8)	
LD50 oral rat	> 2000 mg/kg (Rat)
ATE US (oral)	500.000 mg/kg body weight

Skin corrosion/irritation	: Causes skin irritation. pH: 10.5 - 11
Serious eye damage/irritation	: Causes serious eye damage. pH: 10.5 - 11
Respiratory or skin sensitization	: Not classified
Germ cell mutagenicity	: Not classified

# Gutter Bomb

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
Specific target organ toxicity (single exposure)	: Not classified
Specific target organ toxicity (repeated exposure)	: Not classified
Aspiration hazard	: Not classified
Potential Adverse human health effects and symptoms	: Based on available data, the classification criteria are not met.
Symptoms/injuries after skin contact	: Causes skin irritation.
Symptoms/injuries after eye contact	: Causes serious eye damage.

### SECTION 12: Ecological information

#### 12.1. Toxicity

<b>Disodium metasilicate (6834-92-0)</b>	
LC50 fish 1	210 mg/l (LC50; Equivalent or similar to OECD 203; 96 h; Brachydanio rerio; Semi-static system; Fresh water; Experimental value)
Threshold limit algae 1	207 mg/l (EC50; DIN 38412-9; 72 h; Scenedesmus subspicatus; Fresh water)
<b>Citric acid (77-92-9)</b>	
EC50 Daphnia 1	120 mg/l (EC50; 72 h)
LC50 fish 2	1516 mg/l (LC50; 96 h)
Threshold limit algae 2	640 mg/l (EC0; 168 h)
<b>tetrasodium ethylene diamine tetracetate (64-02-8)</b>	
LC50 fish 1	121 mg/l (LC50; 96 h)
EC50 Daphnia 1	625 mg/l (EC50; 24 h)
LC50 fish 2	396 mg/l
Threshold limit algae 1	> 100 mg/l (EC0; 72 h)

#### 12.2. Persistence and degradability

<b>Gutter Bomb</b>	
Persistence and degradability	Not established.
<b>Disodium metasilicate (6834-92-0)</b>	
Persistence and degradability	Biodegradability: not applicable. No (test)data on mobility of the substance available. Not established.
Biochemical oxygen demand (BOD)	Not applicable
Chemical oxygen demand (COD)	Not applicable
ThOD	Not applicable
<b>Citric acid (77-92-9)</b>	
Persistence and degradability	Readily biodegradable in water. Biodegradable in the soil. No (test)data on mobility of the substance available.
Biochemical oxygen demand (BOD)	0.42 g O <sub>2</sub> /g substance
Chemical oxygen demand (COD)	0.728 g O <sub>2</sub> /g substance
ThOD	0.686 g O <sub>2</sub> /g substance
BOD (% of ThOD)	0.89 (20 days; Literature study)
<b>tetrasodium ethylene diamine tetracetate (64-02-8)</b>	
Persistence and degradability	Not readily biodegradable in water.
Biochemical oxygen demand (BOD)	< 0.002 g O <sub>2</sub> /g substance
Chemical oxygen demand (COD)	0.54 - 0.58 g O <sub>2</sub> /g substance

# Gutter Bomb

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### 12.3. Bioaccumulative potential

<b>Gutter Bomb</b>	
Bioaccumulative potential	Not established.
<b>Disodium metasilicate (6834-92-0)</b>	
Bioaccumulative potential	Bioaccumulation: not applicable. Not established.
<b>Citric acid (77-92-9)</b>	
BCF other aquatic organisms 1	3.2 (BCF; Other)
Log Pow	-1.61 / -1.80, Experimental value; Other
Bioaccumulative potential	Low potential for bioaccumulation (Log Kow < 4).
<b>tetrasodium ethylene diamine tetracetate (64-02-8)</b>	
Log Pow	-2.6
Bioaccumulative potential	Bioaccumulation: not applicable.

### 12.4. Mobility in soil

No additional information available

### 12.5. Other adverse effects

Effect on the global warming : No known effects from this product.  
GWPmix comment : No known effects from this product.  
Other information : Avoid release to the environment.

## SECTION 13: Disposal considerations

### 13.1. Disposal methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.  
Ecology - waste materials : Avoid release to the environment.

## SECTION 14: Transport information

### Department of Transportation (DOT)

In accordance with DOT  
Not applicable

### TDG

Not applicable

### Transport by sea

Not applicable

### Air transport

Not applicable

## SECTION 15: Regulatory information

### 15.1. US Federal regulations

<b>Gutter Bomb</b>
Not listed on the United States TSCA (Toxic Substances Control Act) inventory
<b>Disodium metasilicate (6834-92-0)</b>
Not listed on the United States TSCA (Toxic Substances Control Act) inventory
<b>Citric acid (77-92-9)</b>
Listed on the United States TSCA (Toxic Substances Control Act) inventory
<b>tetrasodium ethylene diamine tetracetate (64-02-8)</b>
Listed on the United States TSCA (Toxic Substances Control Act) inventory

# Gutter Bomb

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### 15.2. International regulations

#### CANADA

No additional information available

#### EU-Regulations

No additional information available

#### National regulations

No additional information available

### 15.3. US State regulations

No additional information available

## SECTION 16: Other information

Revision date : 07/05/2016

Other information : None.

Full text of H-phrases:

H302	Harmful if swallowed
H314	Causes severe skin burns and eye damage
H315	Causes skin irritation
H318	Causes serious eye damage
H319	Causes serious eye irritation
H335	May cause respiratory irritation

HMIS III Rating

Health : 1 Slight Hazard - Irritation or minor reversible injury possible

Flammability : 0 Minimal Hazard - Materials that will not burn

Physical : 0 Minimal Hazard - Materials that are normally stable, even under fire conditions, and will NOT react with water, polymerize, decompose, condense, or self-react. Non-Explosives.

Personal protection : B

B - Safety glasses, Gloves

SDS US (GHS HazCom 2012)

*This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product*