

Product data sheet

Characteristics

QO130M200PRB

Load center, QO, 1 phase, 30 spaces, 30 circuits, 200A convertible main breaker, PoN, NEMA3R, UL



Main

Marketing Trade Name	QO
Product Type	Load Center
Enclosure Type	Weatherproof enclosure
Cover Type	Surface cover

Complementary

Load Center Type	Main breaker
Rated Current	200 A
Number of Spaces	30
Max Short Circuit Current Rating	22 kA
Maximum Number of Single Pole Circuits	40
Maximum Number of Tandem Breakers	10
Number of Phases	1 phase
Wire Size	AWG 4...250 kcmil aluminium/copper
Ground Bar	Grounding bar (ordered separately)
Electrical Connection	Lugs
Wiring Configuration	3-wire
Busbar Material	Tin plated copper: busbar
Enclosure Material	Welded galvanized steel
Surface Finish	Baked enamel grey
Box Number	6R
Height	29.84 in (758 mm)
Width	14.76 in (375 mm)

Environment

Enclosure Rating	NEMA 3R for outdoor
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	10002 - QO PON 1PH LC,12-60 CKT, N3R
Discount Schedule	DE3A
GTIN	00785901229001
Nbr. of units in pkg.	1
Package weight(Lbs)	33.59 lb(US) (15.24 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.00 in (12.7 cm)
Package 1 width	15.80 in (40.132 cm)
Package 1 Length	32.00 in (81.28 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	24
Package 2 Weight	858.00 lb(US) (389.182 kg)
Package 2 Height	45.00 in (114.3 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration