



Main

Marketing Trade Name	QO
Product Type	Load Center
Enclosure Type	Weatherproof enclosure
Cover Type	Surface cover

Complementary

Tightening Torque	Main lugs: 50 lb.in, AWG 6...AWG 2/0, aluminium/copper
Load Center Type	Main lugs
Rated Current	125 A
Number of Spaces	4
Max Short Circuit Current Rating	10 kA
Maximum Number of Single Pole Circuits	8
Maximum Number of Tandem Breakers	4
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 12...AWG 2/0 aluminium AWG 14...AWG 2/0 copper
Ground Bar	Grounding bar included (not installed)
Electrical Connection	Lugs
Wiring Configuration	3-wire
Busbar Material	Tin plated copper: busbar
Enclosure Material	Welded galvanized steel
Surface Finish	Baked enamel grey
Box Number	15R
Height	14.80 in (376 mm)
Width	8.90 in (226 mm)

Environment

Enclosure Rating	NEMA 3R for outdoor
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	00101 - QO 1PH LC,2-8CKT,NEMA 1,3R
Discount Schedule	DE3A
GTIN	00785901484394
Nbr. of units in pkg.	1
Package weight(Lbs)	11.44 lb(US) (5.19 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	4.90 in (12.446 cm)
Package 1 width	10.60 in (26.924 cm)
Package 1 Length	16.20 in (41.148 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------