

PC 622



PREMIUM GRADE STUCCO DUCT TAPE

TYPICAL APPLICATIONS

- For protecting window and door frames during stucco applications
- Can also be used in high performance motorsports
- Also used for heavy duty bundling, holding and splicing

PRODUCT FEATURES

- Excellent holding power
- High tensile strength
- Conformable

CONSTRUCTION

Overall Grade/Function: Premium

Backing: Waterproof polyethylene film with a cloth carrier

Adhesive: Natural rubber

STANDARD WIDTH(S)

1.41 in 1.88 in 2.83 in

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

STANDARD CORE SIZE

3 in

APPLICABLE STANDARDS

Tested in accordance with UL 723

COLOR(S)



BLACK
(BLK)



WHITE
(WHI)



RED
(RED)



SILVER
(SIL)



OLIVE DRAB
(OLV)

PHYSICAL PROPERTIES STANDARD METRIC

Tensile Strength	45 lbs/in width	78.8 N/10 mm
Adhesion to Stainless Steel	54 oz/in width	5.91 N/10 mm
Thickness	12.5 mils	0.32 mm
Elongation	11%	11%
Service Temperature Range	50 F to 200 F	10 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

