

OM3 can support 40GBASE-SR4 / 100GBASE-SR10 in applicable parallel optics networks

10G Duplex Multimode 50/125 OM3 LSZH Fiber Optic Cable (LC/LC), Aqua, 2 m (6 ft.)

MODEL NUMBER: N820-02M



Features

- OM3-rated 2 m (6 ft.) cable with LC/LC connectors
- 10G Ethernet speeds to 300 m @ 850 nm
- High speed, high bandwidth, low cost
- Ideal for fibre channel (SAN) applications
- IEEE 802.3ae and TIA LOMMF compliant
- Use with VCSEL and LED laser light sources
- Backward compatible with legacy LANs

Specifications

OVERVIEW	
UPC Code	037332134660
Technology	Multimode
Optical Mode	OM3
PHYSICAL	
TITOIOAE	
Color	Aqua
Cable Jacket Rating	LSZH
Clad Diameter	125 micron
Core Diameter	50 micron

Highlights

- OM3 rated for 10G Ethernet applications
- Low-smoke, zero halogen
 (LSZH) aqua-colored jacket
- Max 10G distance of 300 m @ 850 nm
- Backward compatible with existing 50/125 fiber

Package Includes

N820-02M 10G Duplex
 Multimode Fiber Optic Cable
 (LC/LC), Aqua, 2 m





2	
6.6	
2	
78.7	
22.86 x 17.78 x 1.27	
9.00 x 7.00 x 0.50	
0.03	
0.06	
COMMUNICATIONS	
10Gbps / 40Gbps / 100Gbps	
LC DUPLEX (MALE)	
LC DUPLEX (MALE)	
LC DUPLEX (MALE)	
SPECIAL FEATURES	
No	
Lifetime limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies