



SECTION 1 - IDENTIFICATION

| | |
|--|---|
| Manufacturer: Black Swan Mfg. Co. 4540 W. Thomas St. Chicago, IL 60651-3318 Tel.: 800-252-5796 Fax: 773-227-3705 Web Site : www.blackswanmfg.com E-mail : info@blackswanmfg.com | For any Transportation or Medical Chemical Emergencies call: <p style="text-align: center;">INFOTRAC</p> <p style="text-align: center;">(800) 535-5053 OR (352) 323-3500</p> <p style="text-align: center;">24 hours per day - 7 days a week</p> |
| Product Name: Big White | Recommended Use: To seal threaded pipes on metal and plastic connections. |

SECTION 2 – HAZARD(S) IDENTIFICATION

| | | | |
|----------------------------|--|--|--|
| Labels None | NFPA | GHS Classification | |
| Signal Word None | <p>HEALTH HAZARD 4 – Deadly 3 – Extreme Danger 2 – Hazardous 1 – Slight Hazardous 0 – Normal Material</p> <p>SPECIFIC HAZARD Oxidizer OX Acid ACID Alkali ALK Corrosive COR Use NO WATER Radioactive </p> | Health | Environmental |
| HMS | | <p>Acute Toxicity: Not Established Skin Irritation: Not Established Eye Irritation: Not Established Skin Sensitization: NO</p> | <p>Acute Aquatic Toxicity: Not Established Chronic Aquatic Toxicity: Not Established</p> |
| | <p>FIRE HAZARD Flash Points 4 – Below 73°F 3 – Below 100°F 2 – Above 100°F, Not exceeding 200°F 1 – Above 200°F 0 – Will not burn</p> <p>REACTIVITY 4 – May detonate 3 – Shock and heat may detonate 2 – Violent chemical change 1 – Unstable if heated 0 – Stable</p> | Physical None | |
| | | Hazardous Statements None | Precautionary Statements P102 : Keep out of reach of children |

SECTION 3 – COMPOSITION / INFORMATION ON INGREDIENTS

| <u>Chemicals</u> | <u>CAS#</u> | <u>EINECS#</u> | <u>REACH</u> <u>Pre-registration Number</u> | <u>Approx %</u> |
|---|-------------|----------------|--|-----------------|
| LIMESTONE CALCIUM CARBONATE | 1317-65-3 | N/A | N/A | 50-70 % |
| HEAVY HYDROTREATED NAPHTHENIC DISTILLATES (PETROLEUM) | 64742-52-2 | N/A | N/A | 20-30% |
| POLYTETRAFLUOROETHYLENE | 9002-84-0 | N/A | N/A | 8-12% |
| TITANIUM DIOXIDE | 13463-67-7 | N/A | N/A | 1-2% |

*Unlisted ingredients are not classified as hazardous according to OSHA 1910.1200.

SECTION 4 – FIRST-AID MEASURES

| |
|---|
| <p>Inhalation: None.</p> <p>Skin: Wash skin thoroughly with soap and water.</p> <p>Eyes: Flush with water for 15 minutes. If irritation persists, get medical attention.</p> <p>Ingestion: DO NOT INDUCE VOMITING. Contact physician immediately.</p> |
|---|

SECTION 5 – FIRE-FIGHTING MEASURES

| |
|---|
| <p>Fire Hazard: None.</p> <p>Combustion Products: None.</p> <p>Extinguishing Media: Carbon Dioxide Gas, Dry Chemical.</p> <p>Unsuitable Extinguishing Media: None known.</p> <p>Protective Equipment: None.</p> <p>Special Fire Fighting Procedures: As appropriate for combustibles in area.</p> |
|---|

GHS SAFETY DATA SHEET

SECTION 6 – ACCIDENTAL RELEASE MEASURES

Personal Precautions: None.
Protective Equipment: None.
Emergency Procedures: None.
Environmental Precautions: None.
Methods for Cleaning Up: Clean up by scrapping and put in a container for disposal.

SECTION 7 – HANDLING AND STORAGE

Handling
Wash thoroughly after handling.

Storage
Store in a dry/cool place.

SECTION 8 – EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Limits

This product is not classified as hazardous according to OSHA 1910.1200.

Engineering Controls: A source of running water to flush or wash the eyes and skin in case of contact. Use local exhaust as needed.
Ventilation: Local ventilation is adequate.
Personal Protective Equipment – Respiratory: None. **Skin:** Rubber Gloves. **Eyes:** Safety Glasses.

SECTION 9 – PHYSICAL & CHEMICAL PROPERTIES

| | | | | | |
|------------------------|-----------------|-------------------------------------|-----------------|-----------------------------|--|
| Appearance: | White Paste | Flash Point: | >300°F | Vapor Pressure: | Not Established |
| Odor: | Oil odor | Specific Gravity: | 1.50 | Flammability: | Not Established |
| pH: | Not Established | Solubility (H₂O): | Insoluble | Flammability Limits: | LEL – Not Established UEL – Not Established |
| Melting Point: | Not Established | Evaporation Rate: | Not Established | | |
| Freezing Point: | Not Established | Vapor Density: | Not Established | | |
| Boiling Point: | Not Established | VOC: | 190 g/l | | |

SECTION 10 – STABILITY AND REACTIVITY

Stability: Stable.
Hazardous polymerization: Will not occur.
Conditions to avoid: Direct contact with open flame.
Incompatible materials: None known.
Hazardous decomposition products: Carbon Dioxide and Carbon Monoxide may be released on burning.

SECTION 11 – TOXICOLOGICAL INFORMATION

Toxicity

This product is not classified as hazardous according to OSHA 1910.1200.

Likely Routes of Exposure: Skin Contact.
Symptoms and Effect - Inhalation: None. **Skin Contact:** None. **Eye Contact:** None. **Ingestion:** None.
Long-Term Effect: None known.
Pre-Existing Conditions: None known.

SECTION 12 – ECOLOGICAL INFORMATION

Ecotoxicity: None known.
Persistence & Degradability: None known.
Bioaccumulative Potential: None known.
Mobility in soil: None known.

SECTION 13 – DISPOSAL CONSIDERATION

Dispose of product or container in accordance with federal, state or local regulations.

SECTION 14 – TRANSPORTATION INFORMATION

D.O.T. (U.S.): Not Regulated.

SECTION 15 – REGULATORY INFORMATION

Precautionary Label Information: None.

Risk Phrases: None.

Safety Phrases: S2-Keep out of reach of children.

SECTION 16 – OTHER INFORMATION

Information on this form is furnished solely for the purpose of compliance with the Occupational Safety and Health Act and shall not be used for any other purpose. Black Swan Mfg. Co. urges the customers receiving this Material Safety Data Sheet to study it carefully to become aware of the hazards, if any, of the product involved. In the interest of safety, you should notify your employees, agents and contractors of the information on the sheets.

DATE: 01/01/2021