

Advanced Specification Sheet

PT-H300 P-touch® Label Maker

*Intuitive, Take-it-Anywhere Labeler with **Brother™ Vivid Bright Display** -
Perfect for labeling in most any environment*



*Prints labels up to 18mm wide,
with up to...*

42pt text

Label shown at actual 18mm wide, 42pt text

Brother™ Vivid Bright Display

- Create and preview work in most any lighting situation

Easy and accurate typing

- Familiar, keyboard-style layout

Durable, laminated labels

- Create labels for indoor or outdoor use

Multi-line printing

- Create detailed labels with up to 5 lines of text and graphics

Create labels with less keystrokes

- Intuitive one-touch keys support quick, easy label formatting

Do more in less time

- Fast print speeds and pre-designed labels support efficient labeling

Flexible power source

- Works with 6 x AA batteries (included), rechargeable battery or AC adapter (both optional)

Get creative

- Hundreds of built-in symbols, fonts, frames and barcodes

Warranty & Support

- 2-year limited warranty and free phone support for the life of your product

Hassle-free application

- Split back tapes for easy peel and stick

Tapes for most any application*

- Standard, extra-strength adhesive, acid free[^], cable and wire, tamper evident, fabric iron-on, super narrow or decorative Simply Stylish



* Additional purchase required.

[^] Claims that adhesive is "acid-free" and/or "photo-safe" are based upon: 1. Satisfactory test results obtained from Photographic Activity Tests per ISO14523 and non-acidic pH tests per TAPPI 509; 2. Certifications from material manufacturers; and 3. Atomic scans of adhesive following removal of backing paper.

Images are for illustrative purposes only. Actual output (such as font and margins) may vary. All trademarks referenced herein are the property of their respective companies.

All specifications subject to change without notice.

Hardware Features:

Display	Graphical with Backlight
Display Size	15 characters x 3 lines
Maximum Tape Width	18mm
Built-in Memory	Up to 50 labels
Keyboard	QWERTY
Tape Cutter	Manual
Maximum Print Speed	20mm/sec.
Maximum Print Resolution	180 dpi
Maximum Print Height	15.8mm
Power Source	6 x AA Batteries (included) Rechargeable Li-ion battery pack (optional) AC Power Adapter (optional)
Auto Power Off	Yes

Software Features:

Number of Fonts	14
Types of Fonts	Helsinki, Brussels, Belgium, Florida, Los Angeles, San Diego, US, Calgary, Atlanta, Adams, Brunei, Sofia, Germany, LetterGothic
Number of Font Styles	10
Number of Font Sizes	7
Maximum Print Lines	5
Number of Font Widths	3
Barcode Printing	9 kinds (CODE39, ITF 2/5, EAN13, EAN8, UPC-A, UPC-E, CODABAR, GS1-128(UCC/EAN128), CODE128)
Built-in Symbols	617
Built-in Frames	99
Auto Numbering	1-9, A-Z, a-z
Repeat Printing	Up to 9 copies
Vertical Printing	Yes
Mirror Printing	Yes
Number of Languages Supported	20

Accessories*:

BA-E001	Optional Rechargeable Li-ion Battery Pack
AD-E001	Optional AC Power Adapter

See next page for a detailed list of compatible tapes.

Carton Contents:

PT-H300 Label Printer
Black on White Standard Laminated TZe Starter Tape 0.7" (18mm) x 13.1' (4m)
6 x AA Alkaline Batteries
Wrist Strap
User's Guide

Setup Information:

UPC Code	012502634966
ITF Barcode	30012502634967
Unit Dimensions	5.2" x 8.4" x 2.6"
Unit Weight	1.5 lbs.
Carton Dimensions	13.6" x 9.8" x 4.0"
Carton Weight	3.1 lbs.
Master Carton Dimensions	14.4" x 12.5" x 10.4"
Master Carton Weight	10.1 lbs.
Master Carton Quantity	3
Pallet Quantity	162
Pallet Tiers	3
Pallet Quantity per Tier	18
Pallet Size	48" x 40"
Pallet + Cartons Height	41.8"
Pallet + Carton Weight	461.1 lbs.
Tariff / Harmonized Code	8443.32.1050
Country of Origin	China



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth. www.brotherearth.com

Scannable Barcode:



012502634966

* Additional purchase required.

Images are for illustrative purposes only. Actual output (such as font and margins) may vary. All trademarks referenced herein are the property of their respective companies. All specifications subject to change without notice.

Standard Adhesive Laminated Tapes:

Standard Adhesive Laminated Tapes stick to virtually any surface and are great for most applications, indoors and out.

TZe-111	6mm (0.23") x 8m (26.2 ft) Black on Clear tape
TZe-211	6mm (0.23") x 8m (26.2 ft) Black on White tape
TZe-315	6mm (0.23") x 8m (26.2 ft) White on Black tape
TZe-121	9mm (0.35") x 8m (26.2 ft) Black on Clear tape
TZe-221	9mm (0.35") x 8m (26.2 ft) Black on White tape
TZe-325	9mm (0.35") x 8m (26.2 ft) White on Black tape
TZe-421	9mm (0.35") x 8m (26.2 ft) Black on Red tape
TZe-131	12mm (0.47") x 8m (26.2 ft) Black on Clear tape
TZe-135	12mm (0.47") x 8m (26.2 ft) White on Clear tape
TZe-231	12mm (0.47") x 8m (26.2 ft) Black on White tape
TZe-232	12mm (0.47") x 8m (26.2 ft) Red on White tape
TZe-334	12mm (0.47") x 8m (26.2 ft) Gold on Black tape
TZe-335	12mm (0.47") x 8m (26.2 ft) White on Black tape
TZe-631	12mm (0.47") x 8m (26.2 ft) Black on Yellow tape
TZe-141	18mm (0.7") x 8m (26.2 ft) Black on Clear tape
TZe-145	18mm (0.7") x 8m (26.2 ft) White on Clear tape
TZe-241	18mm (0.7") x 8m (26.2 ft) Black on White tape
TZe-242	18mm (0.7") x 8m (26.2 ft) Red on White tape
TZe-243	18mm (0.7") x 8m (26.2 ft) Blue on White tape
TZe-344	18mm (0.7") x 8m (26.2 ft) Gold on Black tape
TZe-345	18mm (0.7") x 8m (26.2 ft) White on Black tape
TZe-441	18mm (0.7") x 8m (26.2 ft) Black on Red tape
TZe-541	18mm (0.7") x 8m (26.2 ft) Black on Blue tape
TZe-545	18mm (0.7") x 8m (26.2 ft) White on Blue tape
TZe-641	18mm (0.7") x 8m (26.2 ft) Black on Yellow tape
TZe-741	18mm (0.7") x 8m (26.2 ft) Black on Green tape
TZe-B41	18mm (0.7") x 5m (16.4 ft) Black on Fluorescent Orange tape

Simply Stylish Laminated Tapes:

These brightly colored tapes give your labeling projects that extra color flair.

TZe-MQ835	12mm (0.47") x 5m (16.4 ft) White on Satin Gold tape
TZe-MQ934	12mm (0.47") x 5m (16.4 ft) Gold on Satin Silver tape
TZe-MQG35	12mm (0.47") x 5m (16.4 ft) White on Lime Green tape
TZe-MQP35	12mm (0.47") x 5m (16.4 ft) White on Berry Pink tape

Super Narrow Tape:

This tape is non-laminated and perfect for labeling CD case spines and other narrow spaces.

TZe-N201	3.5mm (0.13") x 8m (26.2 ft) Black on White Non-Laminated tape
-----------------	--

Extra-Strength Laminated Tapes:

These tapes have stronger adhesion strengths than standard adhesive tapes, making them ideal for uneven and rough-textured surfaces, slippery painted metal and plastic surfaces and surfaces exposed to harsh environments.

TZe-S211	6mm (0.23") x 8m (26.2 ft) Black on White Tape with Extra Strength Adhesive
TZe-S121	9mm (0.35") x 8m (26.2 ft) Black on Clear Tape with Extra Strength Adhesive
TZe-S221	9mm (0.35") x 8m (26.2 ft) Black on White Tape with Extra Strength Adhesive
TZe-S621	9mm (0.35") x 8m (26.2 ft) Black on Yellow Tape with Extra Strength Adhesive
TZe-S131	12mm (0.47") x 8m (26.2 ft) Black on Clear Tape with Extra Strength Adhesive
TZe-S135	12mm (0.47") x 8m (26.2 ft) White on Clear Tape with Extra Strength Adhesive
TZe-S231	12mm (0.47") x 8m (26.2 ft) Black on White Tape with Extra Strength Adhesive
TZe-S631	12mm (0.47") x 8m (26.2 ft) Black on Yellow Tape with Extra Strength Adhesive
TZe-S141	18mm (0.7") x 8m (26.2 ft) Black on Clear Tape with Extra Strength Adhesive
TZe-S241	18mm (0.7") x 8m (26.2 ft) Black on White Tape with Extra Strength Adhesive
TZe-S641	18mm (0.7") x 8m (26.2 ft) Black on Yellow Tape with Extra Strength Adhesive
TZe-S941	18mm (0.7") x 8m (26.2 ft) Black on Matte Silver Tape with Extra Strength Adhesive

Wire and Cable Laminated Tapes:

This tape offers labeling solutions for textured surfaces, rounded edges, electrical wiring and audio/visual cables.

TZe-FX231	12mm (0.47") x 8m (26.2 ft) Black on White Flexible ID tape
TZe-FX631	12mm (0.47") x 8m (26.2 ft) Black on Yellow Flexible ID tape
TZe-FX241	18mm (0.7") x 8m (26.2 ft) Black on White Flexible ID tape

Acid-Free Photo Safe Tapes[^]:

Acid-free adhesive laminated tapes are safe for photo-labeling, scrapbooking and other photo-sensitive materials.

TZe-AF131	12mm (0.47") x 8m (26.2 ft) Black on Clear Acid Free Tape
TZe-AF231	12mm (0.47") x 8m (26.2 ft) Black on White Acid Free Tape

Tamper-Evident Laminated Tape:

This tape features a special tell-tale adhesive. If the label is removed, a checkerboard pattern will be left behind. Great for asset management.

TZe-SE4	18mm (0.7") x 8m (26.2 ft) Black on White Security tape
----------------	---

Iron-on Fabric Tape:

This tape can be adhered by ironing.

TZe-FA3	12mm (0.47") x 3m (9.8 ft) Navy Blue on White Fabric tape
----------------	---

Look for: **TZe TAPE**

^{*} Additional purchase required.

[^] Claims that adhesive is "acid-free" and/or "photo-safe" are based upon: 1. Satisfactory test results obtained from Photographic Activity Tests per ISO14523 and non-acidic pH tests per TAPPI 509; 2. Certifications from material manufacturers; and 3. Atomic scans of adhesive following removal of backing paper. Images are for illustrative purposes only. Actual output (such as font and margins) may vary. All trademarks referenced herein are the property of their respective companies. All specifications subject to change without notice.