

BLACK SWAN MFG. CO.

GHS SAFETY DATA SHEET



| | SECTION 1 - ID | ENTIFICATION | | |
|-----------------------------|--|---|--|--|
| Manufacturer: | | For any Transportation or Medical Chemical Emergencies call: | | |
| Black Swan | Mfg. Co. | | | |
| 4540 W. Tho | mas St. | INFOTRAC | | |
| Chicago, IL | 50651-3318 | <u></u> | | |
| Tel.: 800-252 | 2-5796 | (800) 535-5053 OR (352) 323-3500 | | |
| Fax: 773-227 | -3705 | | | |
| Web Site : <u>w</u> | <u>ww.blackswanmfg.com</u> | 24 hours per day - 7 days a week | | |
| E-mail : <u>info</u> | <u>@blackswanmfg.com</u> | | | |
| | SECTION 2 – HAZARI | enamels, etc. D(S) IDENTIFICATION | | |
| Labels | NFPA | GHS Classification | | |
| None Signal Word None | HEALTH HAZARD 4 - Deadly 3 - Extreme Danger 2 - Hazardous 1 - Slight Hazardous 0 - Normal Material SPECIFIC HAZARD 0 0 0 0 F 1 - Slight Hazardous 0 - Normal Material 0 0 0 0 F 1 - Slight Hazardous 0 - Will not burn REACTIVITY | HealthEnvironmentalAcute Toxicity:Not EstablishedAcute Toxicity: Not EstablishedSkin Irritation: Not EstablishedAcute Aquatic Toxicity: Not EstablishedEye Irritation: Not EstablishedChronic Aquatic Toxicity: Not EstablishedSkin Sensitization: NONO | | |
| HMIS | Oxidizer OX Acid ACID Alkali ALK Comparing COP | Physical | | |

| HEALTH | 0 | Corrosive Use NO WATER | Corrosive COR Use NO WATER ₩ | 2 – Violent chemical change | None | |
|--------------|---|---------------------------|---------------------------------|--------------------------------------|---|--------------------------------------|
| FLAMMABILITY | 0 | Radioactive | ¥ | 1 – Unstable if heated 0 – Stable | Hazardous Statements | Precautionary Statements |
| REACTIVITY | 0 | | | | H302: Harmful if swallowed H315: Causes eye irritation | P102 : Keep out of reach of children |

| SECTION 3 – COMPOSITION / INFORMATION ON INGREDIENTS | | | | | | | | |
|--|---------------------------|---|----------------------------------|--|--|--|--|--|
| CAS# | EINECS# | REACH | Approx % | | | | | |
| | | Pre-registration Number | | | | | | |
| 68439-46-3 | N/A | N/A | 1-5% | | | | | |
| 94266-47-4 | N/A | N/A | 1-5% | | | | | |
| | <u>CAS#</u> 68439-46-3 | CAS# EINECS# 68439-46-3 N/A | CAS#EINECS#REACH68439-46-3N/AN/A | | | | | |

*Unlisted ingredients are not classified as hazardous according to OSHA 1910.1200.

SECTION 4 – FIRST-AID MEASURES

Inhalation: None.

Skin: None.

Eyes: Flush with water for 15 minutes. If irritation persists, get medical attention. **Ingestion**: Give 1 or 2 glasses of water. DO NOT INDUCE VOMITING. Get medical attention if you feel unwell.

SECTION 5 – FIRE-FIGHTING MEASURES

Fire Hazard: None. Combustion Products: None. Extinguishing Media: Dry Chemical, Water fog, CO2, Alcohol foam. Unsuitable Extinguishing Media: None known. Protective Equipment: None. Special Fire Fighting Procedures: Flood with water.

GHS SAFETY DATA SHEET

SECTION 6 – ACCIDENTAL RELEASE MEASURES

Personal Precautions: None. Protective Equipment: None. **Emergency Procedures:** None. Environmental Precautions: None.

Methods for Cleaning Up: Clean up by scrapping and put in a container for disposal.

SECTION 7 – HANDLING AND STORAGE

Handling

Keep out of reach of children. Avoid contact with eyes. Do not swallow.

Storage

SECTION 8 – EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Limits

This product is not classified as hazardous according to OSHA 1910.1200.

Engineering Controls: A source of running water to flush or wash the eyes and skin in case of contact. Use local exhaust as needed. Ventilation: Local ventilation is adequate.

Personal Protective Equipment - Respiratory: None. Skin: Gloves. Eyes: Chemical safety goggles or Faceshield.

SECTION 9 – PHYSICAL & CHEMICAL PROPERTIES

Appearance: Odor: pH: Melting Point: Freezing Point: **Boiling Point**:

Flash Point: Specific Gravity: Solubility (H2O): **Evaporation Rate:** Vapor Density: VOC:

253°F 1.01 Soluble 1 0.1 at 20°C $42. \sigma/1$

Vapor Pressure: Flammability: Flammability Limits:

Not Established Not Established LEL - Not Established UEL – Not Established

SECTION 10 – STABILITY AND REACTIVITY

Stability: Stable.

Hazardous polymerization: Will not occur.

Clear/Colorless

Not Established

Not Established

Not Established

100°-230°C

Sweet Citrus

Conditions to avoid: Keep away from open flames and sparks.

Incompatible materials: Avoid contact with strong oxidants, acids and alkalines.

Hazardous decomposition products: CO and CO2 may be liberated if material is burned.

SECTION 11 – TOXICOLOGICAL INFORMATION

Toxicity

This product is not classified as hazardous according to OSHA 1910.1200.

Likely Routes of Exposure: Inhalation, Skin Contact and Ingestion.

Symptoms and Effect – Inhalation: May irritate the nose, throat, respiratory tract. May cause coughing and/or headache. Skin Contact: May cause mild to moderate irritation. May cause burning sensation, redness, swelling, blistering. Prolonged and repeated contact with skin can cause defatting and drying of the skin which may result in skin irritation and dermatitis. Eye Contact: Causes moderate to severe irritation. May cause burning sensation, redness, swelling, blur vision. Ingestion: Harmful if swallowed. May cause vomiting, headache, other medical problems.

Long-Term Effect: None known.

Pre-Existing Conditions: None known.

SECTION 12 – ECOLOGICAL INFORMATION

Ecotoxicity: None known. Persistance & Degradability: None known. Bioaccumulative Potential: None known. Mobility in soil: In normal use, emission of Volatile Organic Compounds (VOC's) to the air takes place, typically at a rate of 42 g/l.

Keep container tightly closed.

GHS SAFETY DATA SHEET

SECTION 13 – DISPOSAL CONSIDERATION

Dispose of product or container in accordance with federal, state or local regulations.

SECTION 14 – TRANSPORTATION INFORMATION

D.O.T. (U.S.): Not Regulated.

SECTION 15 – REGULATORY INFORMATION

Precautionary Label Information: None. **Risk Phrases:** None. **Safety Phrases: S2-**Keep out of reach of children.

SECTION 16 – OTHER INFORMATION

Information on this form is furnished solely for the purpose of compliance with the Occupational Safety and Health Act and shall not be used for any other purpose. Black Swan Mfg. Co. urges the customers receiving this Material Safety Data Sheet to study it carefully to become aware of the hazards, if any, of the product involved. In the interest of safety, you should notify your employees, agents and contractors of the information on the sheets. DATE: 01/01/2021