

GF 0006 (grade)


6 scfm compressed air & gas filter

nano F^{1.1} performance validated compressed air & gas filters are available in a complete range of element grades designed to meet and exceed industry air quality requirements. Filtration performance is tested and validated by an independent laboratory to ISO 12500 standards.



general characteristics	
rated flow (scfm) ⁽¹⁾	6
operating limits	
design operating pressure range (psig) ⁽²⁾	0 to 232
design operating temperature range (°F)	32 to 176
housing construction	
materials	pressure die cast aluminum
finish	E-Coat™ surface treatment (internal & external) powder paint (external)
element construction	
media	borosilicate glass microfiber
end caps	glass filled nylon
replacement element (part no)	GE 0015 (grade)
components	
automatic float drain	GFDK 0050
differential pressure indicator / gauge	-
air circuit	
inlet & outlet connections (NPT)	1/8"

dimensions and weights	
A (ins)	1.97
B (ins)	0.67
C (ins)	6.18
D (ins)	1.10
E (ins)	10.5
weight (lbs)	0.6



element grades	M1	M01	AC
maximum particle size (ISO class) ⁽³⁾	3	1	-
maximum oil content (ISO class) ⁽³⁾	3	2	1
particle removal (microns)	1	0.01	-
max oil carry over at 68°F (ppm or mg/m ³)	0.3	0.01	0.003
design operating temperature range (°F)	32 to 176	32 to 176	32 to 122

(1) at 100 psig. For all other pressures, contact support@n-psi.com

(2) for pressure below 22 psig, order with a GFDK 0050 for models GF 0070 to 1500.

For pressures up to 300 psi use manual drain valve

(3) per ISO 8573.0:2001 (E)

(4) technical specifications subject to change without notice. Direct inquiries to support@n-psi.com or contact 704.897.2182

nano-purification solutions
Charlotte, North Carolina
United States

nano-purification solutions TN
Maryville, Tennessee
United States

nano-purification solutions Canada
St. Catharines, Ontario
Canada

nano-purification solutions Ltd.
Gateshead, Tyne and Wear
United Kingdom

nano-purification solutions GmbH
Erkelenz, Germany

nano-purification solutions Asia
Singapore

Tel: 704.897.2182
Fax: 704.897.2183
Email: support@n-psi.com
Web: www.n-psi.com

features

housing features

- designed in accordance with ASME pressure vessel standards
- carries CRN (Canadian Registration Numbers) for approved use in every province of Canada
- “dead stop” bowl feature provides full closure without overtightening
- optimized seal ensures zero leakage and ease of bowl removal during element replacement
- no tie rod simplifies element change out and reduces access requirements for bowl removal
- comprehensive range of filter mounting accessories
- 10 year housing warranty

element features


- designed to exceed the ISO 8573-1 standards for compressed air purity and the ISO 12500 series international standard for compressed air filter testing
- filtration performance validated and tested in independent laboratories in accordance with international filtration standards
- stainless steel cylinders provide strength, rigidity and corrosion resistance
- pleated filter media provides low differential pressure

accessories



connecting kits

description	fits	part number
connecting kit (2 filters)	GF 0006	GFCK-2 0015
connecting kit (3 filters)	GF 0006	GFCK-3 0015
connecting kit (4 filters)	GF 0006	GFCK-4 0015



wall mounting kits

fits	part number
GF 0006	GFMK 0015