

# GF 1250 (grade)


## 1250 scfm compressed air & gas filter

nano F<sup>1.1</sup> performance validated compressed air & gas filters are available in a complete range of element grades designed to meet and exceed industry air quality requirements. Filtration performance is tested and validated by an independent laboratory to ISO 12500 standards.



general characteristics	
rated flow (scfm) <sup>(1)</sup>	1250
operating limits	
design operating pressure range (psig) <sup>(2)</sup>	22 to 232
design operating temperature range (°F)	32 to 176
housing construction	
materials	pressure die cast aluminum
finish	E-Coat™ surface treatment (internal & external) powder paint (external)
element construction	
media	borosilicate glass microfiber
end caps	glass filled nylon
replacement element (part no)	GE 1250 (grade)
components	
automatic float drain	GFDK 1500
differential pressure indicator / gauge	GFDP 1500
air circuit	
inlet & outlet connections (NPT)	3"

dimensions and weights	
A (ins)	8.66
B (ins)	2.76
C (ins)	33.74
D (ins)	1.18
E (ins)	38.1
weight (lbs)	25.4



element grades	M1	M01	AC
maximum particle size (ISO class) <sup>(3)</sup>	3	1	-
maximum oil content (ISO class) <sup>(3)</sup>	3	2	1
particle removal (microns)	1	0.01	-
max oil carry over at 68°F (ppm or mg/m <sup>3</sup> )	0.3	0.01	0.003
design operating temperature range (°F)	32 to 176	32 to 176	32 to 122

(1) at 100 psig. For all other pressures, contact support@n-psi.com  
 (2) for pressure below 22 psig, order with a GFDK 0050 for models GF 0070 to 1500.  
 For pressures up to 300 psi use manual drain valve  
 (3) per ISO 8573.0:2001 (E)  
 (4) technical specifications subject to change without notice. Direct inquiries to support@n-psi.com or contact 704.897.2182

nano-purification solutions  
 Charlotte, North Carolina  
 United States

nano-purification solutions TN  
 Maryville, Tennessee  
 United States

nano-purification solutions Canada  
 St. Catharines, Ontario  
 Canada

nano-purification solutions Ltd.  
 Gateshead, Tyne and Wear  
 United Kingdom

nano-purification solutions GmbH  
 Erkelenz, Germany

nano-purification solutions Asia  
 Singapore

Tel: 704.897.2182  
 Fax: 704.897.2183  
 Email: support@n-psi.com  
 Web: www.n-psi.com

## features

### housing features

- designed in accordance with ASME pressure vessel standards
- carries CRN (Canadian Registration Numbers) for approved use in every province of Canada
- “dead stop” bowl feature provides full closure without overtightening
- optimized seal ensures zero leakage and ease of bowl removal during element replacement
- no tie rod simplifies element change out and reduces access requirements for bowl removal
- comprehensive range of filter mounting accessories
- 10 year housing warranty

### element features


- designed to exceed the ISO 8573-1 standards for compressed air purity and the ISO 12500 series international standard for compressed air filter testing
- filtration performance validated and tested in independent laboratories in accordance with international filtration standards
- stainless steel cylinders provide strength, rigidity and corrosion resistance
- pleated filter media provides low differential pressure

## accessories



### connecting kits

description	fits	part number
connecting kit (2 filters)	GF 1250	GFCK-2 1500
connecting kit (3 filters)	GF 1250	GFCK-3 1500
connecting kit (4 filters)	GF 1250	GFCK-4 1500



### wall mounting kits

description	fits	part number
wall mounting kit	GF 1250	GFMK 1500