



## Main

Range	PowerLogic
Product name	PowerLogic PM5000
Device short name	PM5563
Product or component type	Power meter

## Complementary

Power quality analysis	Up to the 63rd harmonic
Metering type	Measured neutral current Calculated ground current
Device application	Gateway Power monitoring WAGES metering Multi-tariff
Type of measurement	Current Voltage Frequency Power factor Energy Active and reactive power
Supply voltage	125...250 V DC 100...480 V AC 45...65 Hz
Network frequency	50 Hz 60 Hz
Line Rated Current	1 A 5 A
Type of network	1P + N 3P 3P + N
Maximum power consumption in VA	10 VA 480 V
Ride-through time	35 Ms 120 V AC typical 129 ms 230 V AC typical
Display type	Remote LCD display
Display resolution	128 x 128 pixels
Sampling rate	128 samples/cycle
Measurement current	5...10000 mA
Analogue input type	Voltage 5 MOhm) Current 0.3 mOhm)
Measurement voltage	20...400 V AC 45...65 Hz between phase and neutral 20...690 V AC 45...65 Hz between phases
Frequency measurement range	45...65 Hz
Number of inputs	4 digital

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Measurement accuracy	Apparent power +/- 0.5 % Frequency +/- 0.05 % Active energy +/- 0.2 % Reactive energy +/- 1 % Active power +/- 0.2 % Voltage +/- 0.1 % Power factor +/- 0.005 Current +/- 0.15 °C
Accuracy class	Class 0.2S active energy IEC 62053-22
Number of outputs	2 digital
Information displayed	Tariff 8)
Communication port protocol	Modbus RTU and ASCII 9.6, 19.2 and 38.4 kbauds even/odd or none - 2 wires 2500 V JBUS Modbus TCP/IP 10/100 Mbit/s 2500 V Ethernet Modbus TCP/IP daisy chain BACnet IP
Communication port support	RS485 Ethernet
Communication gateway	Ethernet/serial
Data recording	Time stamping Data logs Maintenance logs Event logs Alarm logs Min/max of instantaneous values
Memory capacity	1.1 MB
Web services	Diagnostic via predefined web pages Real time viewing of data Web server Alarm notification by e-mail
Ethernet service	SNTP client SNMP-Traps
Connections - terminals	Voltage circuit screw terminal block4 Control circuit screw terminal block2 Current transformer screw terminal block6 RS485 link screw terminal block4 Digital input screw terminal block8 Digital output screw terminal block4 Ethernet network RJ45 connector2
Mounting mode	Clip-on
Mounting support	DIN rail
Standards	EN 50470-3 EN 50470-1 IEC 62053-22 IEC 60529 UL 61010-1 IEC 62053-24 IEC 61557-12 ANSI C12.20
Product certifications	CE IEC 61010-1 CULus UL 61010-1 BTL
Width	3.78 in (96 mm)
Depth	2.83 in (72 mm)
Height	3.78 in (96 mm)
Net Weight	15.87 oz (450 g)

## Environment

Electromagnetic compatibility	Limits for harmonic current emissionsclass A IEC 61000-3-2 Conducted RF disturbanceslevel 3 IEC 61000-4-6 Magnetic field at power frequencylevel 4 IEC 61000-4-8 Conducted and radiated emissionsclass B EN 55022 Limitation of voltage changes, voltage fluctuations and flicker in low-voltage IEC 61000-3-3 Electrostatic discharge 8 kVlevel 4 IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test IEC 61000-4-3 Electrical fast transient/burst immunity testlevel 4 IEC 61000-4-4 Surge immunity testlevel 4 IEC 61000-4-5 Voltage dips and interruptions immunity test IEC 61000-4-11
IP degree of protection	Front IP52 IEC 60529 Body IP30 IEC 60529
Relative humidity	5...95 % 122 °F (50 °C)
Pollution degree	2
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Operating altitude	9842.52 ft (3000 m)

## Ordering and shipping details

Category	09777 - POWERLOGIC PM5000 HARDWARE
Discount Schedule	PL1
GTIN	00785901553496
Nbr. of units in pkg.	1
Package weight(Lbs)	2.18 lb(US) (0.99 kg)
Returnability	Yes
Country of origin	IN

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.98 in (15.2 cm)
Package 1 width	4.84 in (12.3 cm)
Package 1 Length	6.77 in (17.2 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	1
Package 2 Weight	34.57 oz (980 g)
Package 2 Height	5.91 in (15 cm)
Package 2 width	6.89 in (17.5 cm)
Package 2 Length	4.92 in (12.5 cm)
Unit Type of Package 3	S03
Number of Units in Package 3	8
Package 3 Weight	18.85 lb(US) (8.552 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

---

Approximate Dimensions

PM5000 Series Remote Display

