

CP 450



HIGH PERFORMANCE GRADE, MODERATE TEMPERATURE MASKING TAPE



TYPICAL APPLICATIONS

- For use in moderate temperature, demanding paint masking applications in the transportation (auto, coaches, buses and marine) and metal fabrication industries
- Also used for wet sanding applications
- Recommended for indoor use only

PRODUCT FEATURES

- Medium-high adhesion
- Excellent adhesion to metal, rubber, plastic and fiberglass
- Clean, flat edges for sharper paint lines
- Conformable for rounding curves and contours
- Residue-free removal
- Temperature-resistant up to 225 F
- Solvent- and moisture-resistant
- Strong, smooth crepe backing is tear- and sliver-resistant

CONSTRUCTION

Overall Grade/Function: High Performance
Backing: Smooth crepe paper
Adhesive: Rubber-based

STANDARD WIDTH(S)

18 mm 24 mm 36 mm 48 mm

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

APPLICABLE STANDARDS

ASTM D 6123/D 6123M-97 (2012), Type I

COLOR(S)



PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	31 lbs/in width	54.3 N/10 mm
Adhesion to Stainless Steel	37 oz/in width	4.05 N/10 mm
Thickness	6.9 mils	0.18 mm
Elongation	10%	10%
Service Temperature Range	32 F to 225 F	0 C to 107 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

