



# SAFETY DATA SHEET

Issue Date 13-Jan-2022

Revision Date 13-Jan-2022

Version 2

## 1. PRODUCT AND COMPANY IDENTIFICATION

### Product identifier

**Product Name** Clean Freeze Freezer Cleaner

### Other means of identification

**Product Code** NL849

**Synonyms** None

### Details of the supplier of the safety data sheet

**Company Name** Nyco Products Company  
5332 Dansher Road,  
Countryside, IL 60525  
(708) 579-8100  
nycoproducts.com

### Emergency telephone number

**Emergency Telephone** Chemtrec 1-800-424-9300

## 2. HAZARDS IDENTIFICATION

### Classification

#### **OSHA Regulatory Status**

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin corrosion/irritation	Category 2
Serious eye damage/eye irritation	Category 1

### Label elements

#### Emergency Overview

# Danger

#### **Hazard statements**

Causes skin irritation

Causes serious eye damage



**Appearance** Clear

**Physical state** Liquid

**Odor** Typical

**Precautionary Statements - Prevention**

Wash face, hands and any exposed skin thoroughly after handling  
Wear protective gloves/protective clothing/eye protection/face protection

**Precautionary Statements - Response**

Specific Treatment (See Section 4 on the SDS)

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

Immediately call a POISON CENTER or doctor/physician

IF ON SKIN: Wash with plenty of soap and water

If skin irritation occurs: Get medical advice/attention

Take off contaminated clothing and wash before reuse

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Call a POISON CENTER or doctor/physician if you feel unwell

IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Drink plenty of water

Immediately call a POISON CENTER or doctor/physician

**Precautionary Statements - Disposal**

Disposal should be in accordance with applicable regional, national and local laws and regulations

**Hazards not otherwise classified (HNOC)****Other Information**

Unknown Acute Toxicity

0 % of the mixture consists of ingredient(s) of unknown toxicity

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Monoethanolamine	141-43-5	1-5	*

\*The exact percentage (concentration) of composition has been withheld as a trade secret.

### 4. FIRST AID MEASURES

**First aid measures****Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

**Eye contact**

Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.

**Inhalation**

Remove to fresh air.

**Ingestion**

Rinse mouth. Drink plenty of water. Never give anything by mouth to an unconscious person. Call a physician immediately.

**Most important symptoms and effects, both acute and delayed****Symptoms**

Any additional important symptoms and effects are described in Section 11: Toxicology Information.

**Indication of any immediate medical attention and special treatment needed****Note to physicians**

Treat symptomatically.

### 5. FIRE-FIGHTING MEASURES

**Suitable extinguishing media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media** Caution: Use of water spray when fighting fire may be inefficient.

**Specific hazards arising from the chemical**

No Information available.

**Explosion data****Sensitivity to Mechanical Impact** None.**Sensitivity to Static Discharge** None.**Protective equipment and precautions for firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**6. ACCIDENTAL RELEASE MEASURES****Personal precautions, protective equipment and emergency procedures****Personal precautions** Ensure adequate ventilation, especially in confined areas.**Environmental precautions****Environmental precautions** Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.**Methods and material for containment and cleaning up****Methods for containment** Prevent further leakage or spillage if safe to do so.**Methods for cleaning up** Pick up and transfer to properly labeled containers.**7. HANDLING AND STORAGE****Precautions for safe handling****Advice on safe handling** Handle in accordance with good industrial hygiene and safety practice.**Conditions for safe storage, including any incompatibilities****Storage Conditions** Keep containers tightly closed in a dry, cool and well-ventilated place.**Incompatible materials** None known based on information supplied.**8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control parameters****Exposure Guidelines**

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Monoethanolamine 141-43-5	STEL: 6 ppm TWA: 3 ppm	TWA: 3 ppm TWA: 6 mg/m <sup>3</sup> (vacated) TWA: 3 ppm (vacated) TWA: 8 mg/m <sup>3</sup> (vacated) STEL: 6 ppm (vacated) STEL: 15 mg/m <sup>3</sup>	IDLH: 30 ppm TWA: 3 ppm TWA: 8 mg/m <sup>3</sup> STEL: 6 ppm STEL: 15 mg/m <sup>3</sup>

*NIOSH IDLH Immediately Dangerous to Life or Health***Other Information** Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).**Appropriate engineering controls****Engineering Controls** Showers, Eyewash stations & Ventilation systems.**Individual protection measures, such as personal protective equipment**

<b>Eye/face protection</b>	Wear safety glasses with side shields (or goggles).
<b>Skin and body protection</b>	Wear protective gloves and protective clothing.
<b>Respiratory protection</b>	If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.
<b>General Hygiene</b>	Handle in accordance with good industrial hygiene and safety practice.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### Information on basic physical and chemical properties

<b>Physical state</b>	Liquid
<b>Appearance</b>	Clear
<b>Color</b>	Yellow
<b>Odor</b>	Typical
<b>Odor threshold</b>	No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	10.5 - 11.5	
Specific Gravity	1.023	
Viscosity	Water Thin	
Melting point/freezing point	-40 °C / -40 Degrees	
Flash point	Above 200°F	
Boiling point / boiling range	>= 100 °C / 212 ° F (at 760 mm Hg) Degrees	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

### Other Information

Density Lbs/Gal	8.54
VOC Content (%)	60

## 10. STABILITY AND REACTIVITY

### Reactivity

No data available

### Chemical stability

Stable under recommended storage conditions.

### Possibility of Hazardous Reactions

None under normal processing.

### Conditions to avoid

Extremes of temperature and direct sunlight.

### Incompatible materials

None known based on information supplied.

**Hazardous Decomposition Products**

None known based on information supplied.

**11. TOXICOLOGICAL INFORMATION****Information on likely routes of exposure****Product Information**

<b>Inhalation</b>	Avoid breathing vapors or mists. Inhalation of vapors in high concentration may cause irritation of respiratory system.
<b>Eye contact</b>	Avoid contact with eyes. Corrosive. Causes serious eye damage.
<b>Skin Contact</b>	Avoid contact with skin. Causes skin irritation.
<b>Ingestion</b>	Do not taste or swallow. May cause gastro intestinal irritation.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Monoethanolamine 141-43-5	= 1720 mg/kg ( Rat )	= 1000 mg/kg ( Rabbit )	-

**Information on toxicological effects**

**Symptoms** No Information available.

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

<b>Sensitization</b>	No Information available.
<b>Germ cell mutagenicity</b>	No Information available.
<b>Carcinogenicity</b>	No Information available.
<b>Reproductive toxicity</b>	No Information available.
<b>STOT - single exposure</b>	No Information available.
<b>STOT - repeated exposure</b>	No Information available.
<b>Target organ effects</b>	Central nervous system, EYES, Respiratory system, Skin.
<b>Aspiration hazard</b>	No Information available.

**Numerical measures of toxicity - Product Information**

**Unknown Acute Toxicity** 0 % of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

<b>ATEmix (oral)</b>	10,370.80 mg/kg
<b>ATEmix (dermal)</b>	13,952.90 mg/kg
<b>ATEmix (inhalation-dust/mist)</b>	30.20 mg/kg

**12. ECOLOGICAL INFORMATION****Ecotoxicity**

0% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Propylene Glycol 57-55-6	19000: 96 h Pseudokirchneriella subcapitata mg/L EC50	41 - 47: 96 h Oncorhynchus mykiss mL/L LC50 static 51400: 96 h Pimephales promelas mg/L LC50 static 51600: 96 h Oncorhynchus mykiss mg/L LC50 static 710: 96 h Pimephales promelas mg/L LC50	1000: 48 h Daphnia magna mg/L EC50 Static
Monoethanolamine 141-43-5	15: 72 h Desmodesmus subspicatus mg/L EC50	114 - 196: 96 h Oncorhynchus mykiss mg/L LC50 static 300 - 1000: 96 h Lepomis	65: 48 h Daphnia magna mg/L EC50

		macrochirus mg/L LC50 static 227: 96 h Pimephales promelas mg/L LC50 flow-through 3684: 96 h Brachydanio rerio mg/L LC50 static 200: 96 h Oncorhynchus mykiss mg/L LC50 flow-through	
--	--	--	--

**Persistence and degradability**

No Information available.

**Bioaccumulation**

Bioaccumulative potential.

Chemical Name	Partition coefficient
Monoethanolamine 141-43-5	-1.91

**Other adverse effects**

No Information available

**13. DISPOSAL CONSIDERATIONS**

**Waste treatment methods**

**Disposal of wastes** Disposal should be in accordance with applicable regional, national and local laws and regulations.

**Contaminated packaging** Do not reuse container.

**14. TRANSPORT INFORMATION**

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

**DOT**

**UN/ID No.** UN1760  
**Proper shipping name** Corrosive liquids, n.o.s.  
**Hazard Class** 8  
**Packing Group** III  
**Special Provisions** IB3, T7, TP1, TP28  
**Description** UN1760, Corrosive liquids, n.o.s (contains Ethanolamine), 8, III  
**Emergency Response Guide Number** 154

**TDG**

**UN/ID No.** UN1760  
**Proper shipping name** Corrosive liquids, n.o.s.  
**Hazard Class** 8  
**Packing Group** III  
**Description** UN1760, Corrosive liquids, n.o.s (contains Ethanolamine), 8, III

**15. REGULATORY INFORMATION**

**International Inventories**

**TSCA** Complies  
**DSL/NDL** Complies

**Legend:**

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

**US Federal Regulations**

**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

**SARA 311/312 Hazard Categories**

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

**CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

**US State Regulations**

**California Proposition 65**

WARNING: This product contains a chemical known to the state of California to cause cancer.

**U.S. State Right-to-Know Regulations**

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Propylene Glycol 57-55-6	X	-	X
Monoethanolamine 141-43-5	X	X	X

**U.S. EPA Label Information**

EPA Pesticide Registration Number Not Applicable

**16. OTHER INFORMATION**

<b>NFPA</b>	Health hazards 2	Flammability 0	Instability 0	Physical and Chemical Properties - Personal protection B
<b>HMIS</b>	Health hazards 2	Flammability 0	Physical hazards 0	

Issue Date 13-Jan-2022

Revision Date 13-Jan-2022

**Revision Note**

No Information available

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**