

# Pipe Joint Compound

---



## DESCRIPTION

**Black Swan's Pipe Joint Compound** is a smooth, grit-free, gray colored pipe joint compound. It seals threaded joints tight and will not crack or crumble. Disassembly months or years later is easy. Contains no lead and is safe for all water systems.

---

## PHYSICAL PROPERTIES

Temperature range use: Gases & Liquid - 15° F (-26° C) to +400° F (+240° C)

Pressure range use: Gases: up to 1,000 PSI Liquids: up to 2,000 PSI

Brushable to: -15° F (-26° C)

Sets up to: Soft-set, non-hardening

Contents: Non-toxic inert oils and carbonate. Contains no lead or silicone.

---

## APPLICATIONS

**Black Swan's Pipe Joint Compound** is recommended for use on all types of metal connections. Not recommended for use on plastic. **Black Swan Pipe Joint Compound** can be used on lines carrying air, water, steam, natural gas, ammonia, brine, dilute acids and alkalis. Not recommended for lines carrying oxygen.

---

## DIRECTIONS

1. Make sure threads are made with a good die.
  2. Clean surface to which compound is to be applied of dirt, oil, moisture, etc.
  3. Apply compound to male threads with brush or applicator. Brush well into threads to ensure leak-free joints.
  4. Assemble joints in usual manner.
- 

## CAUTION

Keep out of reach of children and pets. Do not allow to be taken internally. If swallowed seek immediate medical attention. Do not induce vomiting.

---

### UPC NUMBER AND CARTON INFORMATION

STOCK NO.	SIZE	UPC NUMBER	CARTON CUBIC FEET
02000*	2 oz. tube	0 54647 02000 6	.056
02004^	1/4 pt.	0 54647 02004 4	.222
02005^	1/2 pt.	0 54647 02005 1	.363
02008^	pt.	0 54647 02008 2	.376
02012^	qt.	0 54647 02012 9	.711
02020	gal.	0 54647 02020 4	.776
02021	5 gal.	0 54647 02021 1	1.375
02022	55 gal.	0 54647 02022 8	10.72

\*Hang-tab tubes in display tray

^Brush in can