

Duct Tape



DESCRIPTION

Black Swan's Duct Tape is a silver, black or red polyethylene coated cloth backed tape with a specially formulated pressure sensitive adhesive. It has high tensile strength, excellent adhesion and tack, conforms well to irregular surfaces and will not twist or curl during application. This tape is durable in all-weather conditions. Ideal for sealing duct work, general purpose packaging, and masking PVC pipe. For temporary or permanent use. Contractor grade.

SPECIFICATIONS

THICKNESS (mils)	9
TENSILE STRENGTH (lbs./inch width)	26
ADHESION TO STAINLESS STEEL (oz./inch width)	80
ELONGATION	20%
TEMPERATURE RANGE	32°F To 200°F * TEST METHOD— ASTM D-1000

UPC NUMBER AND CARTON INFORMATION

STOCK NO.	SIZE	UPC NUMBER	CARTON CUBIC FEET
10055*	2" x 60 yds.	0 54647 10055 5	1.042
10056**	2" x 60 yds.	0 54647 10056 2	1.042
10057***	2" x 60 yds.	0 54647 10057 9	1.042
* Silver ** Black *** Red			