




- Create a perfect chamfer on ferrous and non-ferrous metal, including hardened steel, timber, fiberglass and plastics
- Manufactured from M2 HSS for extreme tool life
- Chamfer and deburr bolts, pipe, threaded rod, bar and dowels



Set Description	Part Number	List Price/Piece
E-Z Chamfer M8 ~ M22 / 5/16 ~ 7/8"	2210-822	39.50

For Use On:

- MILD STEEL**
U.S. Grade 2, Metric Grade 4.8
- HARD STEEL**
U.S. Grade 5, Metric Grade 8.8
- VERY HARD STEEL**
U.S. Grade 8, Metric Grade 10.9
- STAINLESS STEEL**
300 Series
- SUPER HARD STEEL**
U.S. Grade ASTM-A574, Metric Grade 12.9



1/4"
HEX DRIVE

Other Features & Benefits:

E-Z Chamfer prevents sparks and burns. When used correctly at low RPM's the tool will not overheat the workpiece. Threads and burrs are sheared off, creating the perfect chamfer for starting a nut or threading die.



DISTRIBUTED BY:

